


### SPECIFICATION

Current Rate:1 AMP  
 Insulation Resistance:1000M  $\Omega$  Min  
 Contact Resistance:30m  $\Omega$  Max  
 Dielectric voltage:600V AC for one minute  
 Operation Temperature:-50°C to +105°C  
 Soldering Temperature:200°C / 5 Sec

### MATERIAL


Insulator:Hi-temp PBT. UL 94V-0  
 Contact material:Phorphos Bronze Jis 5210  
 contact Platred:150U" tin over 40U" nickel






Recommended PCB Layout  
 (PCB TOLERANCE  $\pm 0.05$ )

No. of contact	A $\pm 0.15$	B $\pm 0.15$	C $\pm 0.1$	D $\pm 0.1$	E $\pm 0.1$	F $\pm 0.1$
20	15.50	15.50	5.08	5.08	5.08	5.08
28	18.04	18.04	7.62	7.62	7.62	7.62
32	18.04	20.60	7.62	10.16	7.62	10.16
44	23.48	23.48	12.70	12.70	12.70	12.70
52	25.88	25.88	15.24	15.24	15.24	15.24
68	31.66	31.66	20.32	20.32	20.32	20.32
84	36.66	36.66	25.40	25.40	25.40	25.40

### ORDER INFORMATION



©:Standard Recommend



品名 TITLE	PLCC SOCKET THROUGH HOLE TYPE				
品號 PART NO.	DPLCC-XX-L			日期 DATE	08/08/2005
圖號 DRAWING NO.	DPLCC-XX-L	版本 REV.	B	繪圖 DRAWN	Kent
客戶品號 CUSTOMER P/N		比例 SCALE	FREE	核對 CHECKED	Paul
公差 TOLERANCE	.X $\pm 0.3$ .XX $\pm 0.25$	單位 UNIT	mm	核准 APPROVED	James

AREA	REV.	DESCRIPTION	DATE