

Router - FL MGUARD SMART2 VPN - 2700639

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Router with intelligent firewall, up to 99 Mbps data throughput (wire speed performance), stateful inspection firewall for maximum security and extremely easy configuration, VPN according to IPsec standard, hardware encryption with up to 35 Mbps

Product Description

SmallThe mGuard smart from Innominate features maximum possible security and performance in a minimum amount of space. It has never been easier to protect critical company computers, machines or any other IP connection reliably and securely from attacks.StrongThe mGuard smart security appliance combines the extremely powerful mGuard hardware platform with proven mGuard firmware. Based on a robust embedded Linux system from Innominate, this combination integrates four perfectly coordinated security components: a bidirectional stateful firewall, a flexible NAT router, a high-security VPN gateway, and industrial protection against malware as an option.SmartWith its rugged housing and uncomplicated power supply via any USB port, the mGuard smart is the ideal solution for the mobile protection of critical company resources. Changes to the location and infrastructure can be implemented quickly and inexpensively.Focus on securityThe mGuard smart is particularly suitable for the mobile and stationary protection of workstations and environments close to the production process with low requirements for industrial hardening. It can be used as a secure firewall between office and production networks, as a remote maintenance client or as a security router for small workgroups.Secure remote maintenanceFor software-independent remote maintenance scenarios, the mGuard smart can be used as a mobile VPN client and as a temporary VPN connection for secure remote machine maintenance via IPsec-encrypted VPN tunnels. It is particularly ideal for medium-scale machine and system engineering when used as an inexpensive teleservice infrastructure for connecting machines, controllers or mobile technicians.

Product Features

- VPN module for mobile use

Key commercial data

package_quantity	1
GTIN	4046356616591

Technical data

Dimensions

Width	77 mm
Height	27 mm
Depth	115 mm

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 % (no condensation)

Interfaces

Interface 1	Ethernet
No. of ports	2 (RJ45)

Router - FL MGUARD SMART2 VPN - 2700639

Technical data

Interfaces

Connection method	RJ45
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity

Function

Basic functions	Firewall/router for office use or mobile service technicians
Management	Web-based management, SNMP
Supported browsers	HTTPS support required
Processor	Freescale processor with 300 MHz clocking
Status and diagnostic indicators	LEDs: In combination for boot process, heartbeat, system error, Ethernet status, recovery mode

Network expansion parameters

Maximum conductor length ((twisted pair)	100 m
-------------------------------------------------	-------

Supply voltage

Supply voltage	5 V DC (from USB interface)
-----------------------	-----------------------------

General

Type AX	Stand-alone
Weight	160 g

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 41.94304 Mbps (Router mode, VPN bidirectional throughput)
Virtual private network (VPN) throughput	max. 27.262976 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	10 (Up to 250 with license possible)
Encryption methods	DES, 3DES, AES-128, -192, -256
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1
1:1 Network Address Translation (NAT) in the VPN	Supported
Firewall data throughput	max. 130.023424 Mbps (Router mode, default firewall rules, bidirectional throughput)
Firewall data throughput	max. 60.817408 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	NAT, 1:1-NAT, Port Forwarding

Router - FL MGUARD SMART2 VPN - 2700639

Technical data

classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	19030101
eCl@ss 6.0	19170103
eCl@ss 7.0	19170103
eCl@ss 8.0	19170103

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC001478
ETIM 5.0	EC001478

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601

accessories

Patch cable

FL CAT5 PATCH 0,3 - 2832250



FL CAT5 PATCH 0,5 - 2832263



Router - FL MGUARD SMART2 VPN - 2700639

accessories

FL CAT5 PATCH 1,0 - 2832276



FL CAT5 PATCH 1,5 - 2832221



FL CAT5 PATCH 2,0 - 2832289



FL CAT5 PATCH 3,0 - 2832292



FL CAT5 PATCH 5,0 - 2832580



FL CAT5 PATCH 7,5 - 2832616



Router - FL MGUARD SMART2 VPN - 2700639

accessories

FL CAT5 PATCH 10,0 - 2832629



FL CAT6 PATCH 12,5 - 2891369



FL CAT6 PATCH 15,0 - 2891372



FL CAT6 PATCH 20,0 - 2891576



Protective cap

FL RJ45 PROTECT CAP - 2832991



Connector set

Router - FL MGUARD SMART2 VPN - 2700639

accessories

FL PLUG RJ45 GR/2 - 2744856



FL PLUG RJ45 GN/2 - 2744571



Universal tools

FL CRIMPTOOL - 2744869



Patch panel

FL PF 2TX CAT5E - 2891165



FL PF 8TX CAT5E - 2891178



Media converter

Router - FL MGUARD SMART2 VPN - 2700639

accessories

FL MC EF 1300 MM SC - 2902853



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>