

Antenna - RAD-ISM-2400-ANT-OMNI-9-0 - 2867623

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Omnidirectional antenna, 2.4 GHz, 9 dBi, linear vertical, N (female), IP65, 50 Ω impedance

Product Features

- For mobile applications with a longer range

Key commercial data

package_quantity	1
GTIN	4017918939007

Technical data

Dimensions

Width	25 mm
Height	625 mm

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

General

Frequency range	2.4 GHz
Frequency range	2.4 GHz
Horizontal beamwidth	360 °
Vertical beamwidth	15 °
Impedance	50 Ω
Gain	9 dBi
Connection method	N (female)

classifications

eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27250312
eCl@ss 5.0	19070102
eCl@ss 5.1	19070102

Antenna - RAD-ISM-2400-ANT-OMNI-9-0 - 2867623

classifications

eCl@ss

eCl@ss 6.0	19070102
eCl@ss 7.0	19070102
eCl@ss 8.0	19070102

ETIM

ETIM 2.0	EC000416
ETIM 3.0	EC001698
ETIM 4.0	EC001698
ETIM 5.0	EC001698

UNSPSC

UNSPSC 6.01	43171611
UNSPSC 7.0901	43221706
UNSPSC 11	43171611
UNSPSC 12.01	43221706
UNSPSC 13.2	43221706

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>