

Antenna cable - RAD-PIG-RSMA/N-1 - 2903264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Antenna cable, 1 m in length; N (male) -> RSMA (male), impedance 50 ohms

The illustration shows a version of the product

Product Description

Coaxial antenna adapter cable, N (male) to RSMA (male), 50 Ω, 1.0 m

Key commercial data

package_quantity	1
GTIN	4046356743679

Technical data

Dimensions

Fixed cable length	1 m
External diameter	4.95 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
--	------------------

General

Connection method	RSMA (male)
Connection method	N (male)
Cable type	195
Cable, attenuation	0.55 dB @ 915 MHz
Cable, attenuation	0.80 dB @ 2.44 GHz
Cable, attenuation	1.10 dB @ 5.80 GHz
Minimum bending radius	12.70 mm

classifications

eCl@ss

eCl@ss 4.0	27230207
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 5.1	27061802

Antenna cable - RAD-PIG-RSMA/N-1 - 2903264

classifications

eCl@ss

eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC000019
ETIM 5.0	EC001682

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	43223108
UNSPSC 11	39121008
UNSPSC 12.01	43223108
UNSPSC 13.2	43223108

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>