

**Bolt-type screw terminals
WF 6/2BZ**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications.

Connections from 10 mm² to 300 mm² are possible. The conductors are attached to the terminals using crimped cable lugs and each connection secured by tightening the hexagonal nut.

Bolt-type screw terminals with threads from M5 to M16 can be used depending on the conductor cross-section. A low voltage drop and the use of a self-extinguishing material with a V-0 (UL 94) flammability rating guarantee maximum safety.

All bolt-type screw terminals have been tested according to international railway standards (EN 50343, EN 50155, NF F61-017, NF16-101; Ria 20) and comply with the requirements of those standards.

General ordering data

Type	WF 6/2BZ
Order No.	1789770000
Version	Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 35 mm ² , Threaded stud connection
GTIN (EAN)	4032248251124
Qty.	25 pc(s).

Bolt-type screw terminals WF 6/2BZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	67 mm	Width	17.8 mm
Height	54.5 mm	Height of lowest version	56 mm
Net weight	66.754 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Explosion-tested version	No	Open sides	Open
Type of mounting	Snap-on		

CSA ratings data

Certificate No. (CSA)	200039-1244019	Voltage size C (CSA)	1000 V
Current size C (CSA)	115 A	Wire cross section max. (CSA)	2 AWG

Clampable wires (rated connection)

Type of connection	Threaded stud connection	Clamping range, rated connection, min.	2.5 mm ²
Clamping range, rated connection, max.	35 mm ²	Tightening torque, min.	3 Nm
Tightening torque, max.	6 Nm	Wire connection cross section, finely stranded, max.	35 mm ²
Wire connection cross-section, finely stranded, min.	2.5 mm ²		

Rated data

Rated cross-section	35 mm ²	Rated voltage	1,000 V
Rated impulse withstand voltage	8 kV	Rated current	125 A
Current at maximum wires	125 A	Pollution severity	3

Stud connection

Tightening torque, min.	3 Nm	Tightening torque, max.	6 Nm
Stud size for spade connection	M 6	Cable lug to DIN 46234	2.5...35 mm ²
Cable lug to DIN 46235	6...25 mm ²	Clamping range, bolted connection , min.	2.5 mm ²
Clamping range, bolted connection , max.	35 mm ²		

UL ratings data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	2 AWG
Current size C (cURus)	115 A	Voltage size C (cURus)	1000 V
Certificate No. (UR)	E60693	Voltage size C (UR)	1000 V
Current size C (UR)	115 A	Conductor size Factory wiring max. (UR)	2 AWG
Conductor size Factory wiring min. (UR)	14 AWG	Conductor size Field wiring max. (UR)	2 AWG

Bolt-type screw terminals WF 6/2BZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	Bolt-type screw terminals	Type of connection	Threaded stud connection
Number of levels	1	No. of clamping points per level	3
Levels cross-connected internally	No	Mounting rail	TS 35

Classifications

ETIM 3.0	EC002020	UNSPSC	30-21-18-01
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20

Product information

Descriptive text ordering data	1000 VDC rated voltage tested. 1000 V UL and CSA for use groups B and C: can be used with isolating DIN rails and when using WTW-type partitions.
Descriptive text accessories	With WTW...2300 made from epoxy resin, rated current 2300 V according to prelim. EN 50124 pt 1

Approvals

Approvals



ROHS Conform

Bolt-type screw terminals WF 6/2BZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

