Cable glands
VP M20 K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M20 K54
Order No.	1776910000
Version	Cable glands, cable glands, Polyamid 6 (PA6 - GF30), RAL 7035, M 20, IP 54
GTIN (EAN)	4032248156351
Qty.	100 pc(s).

Cable glands
VP M20 K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	6.5 mm	Net weight	2.1 g

General information

Cable gland	metric	Colour code	RAL 7035
DIN	DIN 46320 (for PG thread)	External thread	M 20
Head diameter	24 mm	Length of thread	7 mm
Material	Polyamid 6 (PA6 - GF30)	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Protection degree with GWDR	IP 65	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000032	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-10	eClass 6.2	27-14-91-10
eClass 7.1	27-14-91-10		

Product information

Descriptive text ordering data	Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver.
Descriptive text technical data	Optional sealing ring

Approvals

ROHS	Conform