

Antenna cable - PSI-CAB-GSM/UMTS- 5M - 2900980

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



GSM/UMTS antenna cable, 5 m long; SMA (male) -> SMA (female), 50 Ohm impedance

Key commercial data

package_quantity	1
GTIN	4046356568906

Technical data

Dimensions

Fixed cable length	5 m
External diameter	5.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

General

Connection 1	Connector connection
Connection method	SMA (male)
Connection 2	Connector connection
Connection method	SMA (female)
Cable, attenuation	Approx. 0.23 dB/m at 850 MHz
Cable, attenuation	Approximately 0.24 dB/m at 900 MHz
Cable, attenuation	Approximately 0.35 dB/m at 1.8 GHz
Cable, attenuation	Approximately 0.39 dB/m at 2.1 GHz
Outer sheath, material	LSFH
Minimum bending radius	82.00 mm

classifications

eCl@ss

eCl@ss 4.0	27240490
eCl@ss 4.1	27240490
eCl@ss 5.0	27242208
eCl@ss 5.1	27242208

Antenna cable - PSI-CAB-GSM/UMTS- 5M - 2900980

classifications

eCl@ss

eCl@ss 6.0	19070490
eCl@ss 7.0	19070490
eCl@ss 8.0	19070490

ETIM

ETIM 3.0	EC000310
ETIM 4.0	EC001682
ETIM 5.0	EC001682

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	43223108
UNSPSC 11	39121008
UNSPSC 12.01	43223108
UNSPSC 13.2	43223108

Drawings