

Antenna - RAD-ISM-2400-ANT-OMNI-6-0 - 2885919

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Omnidirectional antenna, 2.4 GHz, 6 dBi, linear vertical, N (female), IP55, 50 Ohm impedance

Product Features

- For mobile applications with a longer range

Key commercial data

| | |
|------------------|---------------|
| package_quantity | 1 |
| GTIN | 4046356146319 |

Technical data

Dimensions

| | |
|--------|--------|
| Width | 22 mm |
| Height | 250 mm |

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP55 |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 75 °C |

General

| | |
|----------------------|---------------------|
| Frequency range | 2.4 GHz |
| Frequency range | 2.4 GHz ... 2.5 GHz |
| Horizontal beamwidth | 360 ° |
| Vertical beamwidth | 30 ° |
| Impedance | 50 Ω |
| Gain | 6 dBi |
| Connection method | N (female) |

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250312 |
| eCl@ss 4.1 | 27250312 |
| eCl@ss 5.0 | 19070102 |
| eCl@ss 5.1 | 19070102 |

Antenna - RAD-ISM-2400-ANT-OMNI-6-0 - 2885919

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 6.0 | 19070102 |
| eCl@ss 7.0 | 19070102 |
| eCl@ss 8.0 | 19070102 |

ETIM

| | |
|-----------------|----------|
| ETIM 2.0 | EC000416 |
| ETIM 3.0 | EC001698 |
| ETIM 4.0 | EC001698 |
| ETIM 5.0 | EC001698 |

UNSPSC

| | |
|----------------------|----------|
| UNSPSC 6.01 | 43171611 |
| UNSPSC 7.0901 | 43221706 |
| UNSPSC 11 | 43171611 |
| UNSPSC 12.01 | 43221706 |
| UNSPSC 13.2 | 43221706 |

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>