

Terminal markers WS 10/5 MC M NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	WS 10/5 MC M NE WS
Order No.	1792000000
Version	Terminal markers, MultiCard, 10 x 5 mm, Polyamide 66, Colour: White
GTIN (EAN)	4032248223862
Qty.	720 pc(s).

Terminal markers WS 10/5 MC M NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	10 mm	Width	5 mm
Net weight	0.176 g		

General data

Application/manufacture	Allen-Bradley	Colour	White
Colour of printing	Black	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	UL 94 flammability rating	V-2

Connector markers

Pitch in mm (P)	5 mm
-----------------	------

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

ROHS	Conform
------	---------

Downloads


M-Print® PRO configuration file	mc_ws_10_5_mcf.zip
---------------------------------	------------------------------------

Terminal markers WS 10/5 MC M NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Example of use



Drawing

