

# Antenna cable - PSI-CAB-GSM/UMTS-10M - 2900981

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



GSM/UMTS antenna cable, 10 m long; SMA (male) -> SMA (female), 50 Ohm impedance

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356568890

## Technical data

### Dimensions

<b>Fixed cable length</b>	10 m
<b>External diameter</b>	5.50 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 85 °C
<b>Ambient temperature (storage/transport)</b>	-40 °C ... 85 °C

### General

<b>Connection 1</b>	Connector connection
<b>Connection method</b>	SMA (male)
<b>Connection 2</b>	Connector connection
<b>Connection method</b>	SMA (female)
<b>Cable, attenuation</b>	Approx. 0.23 dB/m at 850 MHz
<b>Cable, attenuation</b>	Approximately 0.24 dB/m at 900 MHz
<b>Cable, attenuation</b>	Approximately 0.35 dB/m at 1.8 GHz
<b>Cable, attenuation</b>	Approximately 0.39 dB/m at 2.1 GHz
<b>Outer sheath, material</b>	LSFH
<b>Minimum bending radius</b>	82.00 mm

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27240490
<b>eCl@ss 4.1</b>	27240490
<b>eCl@ss 5.0</b>	27242208
<b>eCl@ss 5.1</b>	27242208

## Antenna cable - PSI-CAB-GSM/UMTS-10M - 2900981

### classifications

#### eCl@ss

<b>eCl@ss 6.0</b>	19070490
<b>eCl@ss 7.0</b>	19070490
<b>eCl@ss 8.0</b>	19070490

#### ETIM

<b>ETIM 3.0</b>	EC000310
<b>ETIM 4.0</b>	EC001682
<b>ETIM 5.0</b>	EC001682

#### UNSPSC

<b>UNSPSC 6.01</b>	30211506
<b>UNSPSC 7.0901</b>	43223108
<b>UNSPSC 11</b>	39121008
<b>UNSPSC 12.01</b>	43223108
<b>UNSPSC 13.2</b>	43223108

### Drawings