

# Antenna cable - RAD-PIG-RSMA/N-2 - 2903265

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Antenna cable, 2 m in length; N (male) -> RSMA (male), impedance 50 ohms

The illustration shows a version of the product

## Product Description

Coaxial antenna adapter cable, N (male) to RSMA (male), 50 Ω, 2.0 m

## Key commercial data

package_quantity	1
GTIN	4046356743457

## Technical data

### Dimensions

Fixed cable length	2 m
External diameter	4.95 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### General

Connection method	RSMA (male)
Connection method	N (male)
Cable type	195
Cable, attenuation	0.87 dB @ 915 MHz
Cable, attenuation	1.35 dB @ 2.44 GHz
Cable, attenuation	2.00 dB @ 5.80 GHz
Minimum bending radius	12.70 mm

## classifications

### eCl@ss

eCl@ss 4.0	27230207
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 5.1	27061802

## Antenna cable - RAD-PIG-RSMA/N-2 - 2903265

### classifications

#### eCl@ss

<b>eCl@ss 6.0</b>	27242208
<b>eCl@ss 7.0</b>	27242208
<b>eCl@ss 8.0</b>	27242208

#### ETIM

<b>ETIM 3.0</b>	EC001423
<b>ETIM 4.0</b>	EC000019
<b>ETIM 5.0</b>	EC001682

#### UNSPSC

<b>UNSPSC 6.01</b>	30211506
<b>UNSPSC 7.0901</b>	43223108
<b>UNSPSC 11</b>	39121008
<b>UNSPSC 12.01</b>	43223108
<b>UNSPSC 13.2</b>	43223108

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>