

**Bolt-type screw terminals  
WTW WF6 2300**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

**General ordering data**

|            |                                                         |
|------------|---------------------------------------------------------|
| Type       | WTW WF6 2300                                            |
| Order No.  | <a href="#">1781230000</a>                              |
| Version    | Bolt-type screw terminals, Separation plate, grey, 2 mm |
| GTIN (EAN) | 4032248241125                                           |
| Qty.       | 20 pc(s).                                               |

## Bolt-type screw terminals WTW WF6 2300

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|                            |          |                 |            |
|----------------------------|----------|-----------------|------------|
| Width                      | 2 mm     | Width (inches)  | 0.079 inch |
| Height                     | 101.8 mm | Height (inches) | 4.008 inch |
| Depth                      | 58.45 mm | Depth (inches)  | 2.301 inch |
| Mounting dimension - width | 2 mm     | Net weight      | 18.4 g     |

### Temperatures

|                                   |        |                                  |               |
|-----------------------------------|--------|----------------------------------|---------------|
| Operating temperature range, max. | 160 °C | Storage temperature, max.        | 40 °C         |
| Storage temperature, min.         | 10 °C  | Storage temperature              | 10 °C...40 °C |
| Continuous operating temp., min.  | -60 °C | Continuous operating temp., max. | 160 °C        |

### Material data

|                           |             |        |      |
|---------------------------|-------------|--------|------|
| Material                  | Epoxy resin | Colour | grey |
| UL 94 flammability rating | V-0         |        |      |

### System specifications

|         |                            |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

### Additional technical data

|                     |                 |         |    |
|---------------------|-----------------|---------|----|
| Installation advice | Direct mounting | Snap-on | No |
|---------------------|-----------------|---------|----|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | ETIM 4.0   | EC000886    |
| ETIM 5.0   | EC000886    | ETIM 6.0   | EC000886    |
| UNSPSC     | 30-21-18-27 | eClass 5.1 | 27-14-11-33 |
| eClass 6.2 | 27-14-11-33 | eClass 7.1 | 27-14-11-33 |
| eClass 8.1 | 27-14-11-33 | eClass 9.0 | 27-14-11-92 |
| eClass 9.1 | 27-14-11-33 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                     |
|--------------------|-------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>        |
| Engineering Data   | <a href="#">STEP</a>                |