Base strip - IPCV 5/ 4-G-7,62 - 1708844

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The figure shows a 5-pos. version of the product

Header, Nominal current: 41 A, Rated voltage (III/2): 630 V, Number of positions: 4, Pitch: 7.62 mm, Color: green, Contact surface: Tin, Assembly: Soldering

Product Features

- Asymmetrical arrangement of solder pins to prevent mismatching
- Inverted vertical IPC 5 headers for implementing a touch-proof PCB output or a PCB/PCB connection (in combination with PC 5 base strips)
- Maximum contact reliability due to integrated double steel spring

Key commercial data

package_quantity	50
GTIN	4046356089784

Technical data

Dimensions

Length	12.8 mm
Pitch	7.62 mm
Dimension a	22.86 mm
Pin dimensions	1,2x0,8
Pin spacing	7.62 mm
Hole diameter	1.3 mm

General

Range of articles	IPCV 5/..-G
Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	630 V
Rated voltage (III/2)	630 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	41 A
Maximum load current	41 A

Base strip - IPCV 5/ 4-G-7,62 - 1708844

Technical data

General

Insulating material	PA
Inflammability class according to UL 94	V0
Color	green
Number of positions	4

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized

Usegroups	**B**	**C**	**D**
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	41 A	41 A	5 A
mm²/AWG/kcmil			

Base strip - IPCV 5/ 4-G-7,62 - 1708844

approvals


cUL Recognized

Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	41 A	41 A	5 A
mm²/AWG/kcmil			

cULus Recognized


Drawings

Drilling diagram



Base strip - IPCV 5/ 4-G-7,62 - 1708844

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com