

SKH D32 LP 5/16 RH2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Plug-in card holders are used to adapt cards from the Euro format (19") to connectors in compliance with IEC 603/ DIN 41612 and DIN 41617.

Plug-in card holders consist of the following components:

- Circuit board with standard connectors and inserts with clamping-yoke connection.
- Flange housing and holder/pull-out mechanism for the circuit card.
- Plug-in card and mounting foot for attaching to mounting rail or directly to panel.

The plug-in card holders are normally used in the following cases:

- For quick adaptation in industrial applications of different 19" modules, and for avoiding the expense of a 19" rack.
- When there are only a few cards to install and connect.
- The circuit board is located in a remote position where the cabling cannot be easily handled.
- An older system needs to be updated with additional electronics modules.
- For test devices, production processes and laboratories: where circuit boards needs to be swapped out quickly and connections must be easy to handle.

General ordering data

Type	SKH D32 LP 5/16 RH2
Order No.	0586761001
Version	Interface, Plug-in connector, acc. to DIN 41612 female, 32D
GTIN (EAN)	4032248046270
Qty.	1 pc(s).

SKH D32 LP 5/16 RH2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	50.8 mm	Width	131 mm
Height	144 mm	Net weight	186 g

Temperatures

Operating temperature	0...+55°C	Storage temperature	-40...+60 °C
-----------------------	-----------	---------------------	--------------

Connection data

Connection (field side)	LP 5.08mm	Connection on control side	Plug-in connector, acc. to DIN 41612 female
Number of poles (control side)	32-pole female	Type (control side)	32D
Contact assembly	a and c	Design of the pluggable board	100x160 mm euro format for 19" racks

Rating data

Rated voltage	250 V UC	Rated current per connection	4 A
---------------	----------	------------------------------	-----

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	250 V
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.1 kV	Insulation test voltage	1.2 kVAC

Connection field

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	0.5 mm ²	Sleeve with plastic collar, max.	2.5 mm ²
Min. wire cross-section, AWG [field]	AWG 26	Max. wire cross-section, AWG [field]	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Classifications

ETIM 3.0	EC001419	UNSPSC	30-21-18-01
eClass 5.1	27-24-22-04	eClass 6.2	27-24-22-04
eClass 7.1	27-14-11-52		

Product information

Descriptive text accessories	Kit for connection to TS35: Installation motherboard 2054280000 and mounting foot to TS35 0687900000
------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------

SKH D32 LP 5/16 RH2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

