

**SAIL-VSA-M8W-3-1.5U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



This valve plug has a transparent housing with an integral seal. The connection cross-section corresponds to 0.5 mm<sup>2</sup> and can therefore be connected directly to our SAI IDC distributor. The operating status of the valve plug is indicated by an LED. All the valve plugs have a protective circuit. The Weidmüller range of products comprises valve plugs type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | SAIL-VSA-M8W-3-1.5U        |
| Order No.  | <a href="#">1026190150</a> |
| Version    | Valve plug, A              |
| GTIN (EAN) | 4032248751297              |
| Qty.       | 1 pc(s).                   |

## SAIL-VSA-M8W-3-1.5U

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |      |
|------------|------|
| Net weight | 84 g |
|------------|------|

### Technical specifications for cable

|                 |       |                    |                      |
|-----------------|-------|--------------------|----------------------|
| No. of poles    | 3     | Core cross-section | 0.34 mm <sup>2</sup> |
| Sheath material | PUR   | Sheathing colour   | Black                |
| Cable length    | 1.5 m |                    |                      |

### General technical data

|                              |                             |                   |                         |
|------------------------------|-----------------------------|-------------------|-------------------------|
| Coding                       | Design A (18 mm), M8 = none | Protection degree | IP 67 (when screwed in) |
| Contact surface              | tinned                      | LED               | Yes                     |
| Rated voltage                | 24 V                        | Rated current     | 4 A                     |
| Temperature range of housing | -25...+80 °C                |                   |                         |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| eClass 6.2 | 27-06-91-90 | eClass 7.1 | 27-06-91-90 |
|------------|-------------|------------|-------------|

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |