

ADAM-6050

ADAM-6051

ADAM-6052

18-channel Isolated Digital I/O Module

16-channel Isolated Digital I/O w/Counter Module

16-channel Source Type Digital I/O Module



ADAM-6050

CE FCC



ADAM-6051

CE FCC



ADAM-6052

CE FCC

Specifications

General

- **Channels** 12 DI, 6 DO
- **Digital Input**
 - Dry Contact: Logic level 0: close to GND
Logic level 1: open
 - Wet Contact: Logic level 0: +3 V max
Logic level 1: +10~30 V_{DC}
 - Counter: Up to 3 kHz
Frequency: 0.3 ~ 3000 Hz max.
- **Digital Output** Open Collector to 30 V
200 mA max. load
Pulse Output: Up to 5 kHz

Ordering Information

- **ADAM-6050** 18-channel isolated Digital I/O module

Specifications

General

- **Channels** 12 DI, 2 DO, 2 Counter
- **Counter**
 - Maximum Count: 4,294,967,285(32 bit)
 - Input frequency: 0.3 ~ 4500 Hz max. (frequency mode)
4500 Hz max. (counter mode)
 - Isolation voltage: 2000 V_{RMS}
 - Modes: Counter, Frequency
- **Digital Input**
 - Dry Contact: Logic level 0: close to GND
Logic level 1: open
 - Wet Contact: Logic level 0 : +3 V max
Logic level 1 : +10 V to 30 V_{DC}
 - Counter: Up to 4.5 kHz
Frequency: Up to 3 kHz
- **Digital Output** Open Collector to 30 V
200 mA max. load
Pulse Output: up to 5 kHz

Ordering Information

- **ADAM-6051** 16-channel isolated Digital I/O with counter module

Specifications

General

- **Channels** 8 DI, 8 DO
- **Digital Input**
 - Dry Contact: Logic level 0: close to GND
Logic level 1: open
 - Wet Contact: Logic level 0 : +3 V max
Logic level 1 : +10 V to 30 V_{DC}
- **Digital Output: (Source Type)** V_{DC}: 35 V
Current: 1 A

Ordering Information

- **ADAM-6052** 16-channel Source Type Digital I/O module

Common Specifications

General

- **Certifications** CE, FCC class A
- **Dimensions (WxHxD)** 70 x 112 x 25 mm
- **Connectors** 1 x RJ-45 (LAN)
Plug-in screw terminal block (I/O, and power)
- **Enclosure** ABS+PC
- **LAN** 10/100Base-T

- **LED Indicators** Power and communication
- **Mounting** DIN 35 rail, stack, wall
- **Power Consumption** 2 W (typical)
- **Power Input** Unregulated 10~30 V_{DC}

Protection

- **Power Reversal Protection**

- **Optical Isolation** 2,000 V_{RMS}

Environment

- **Humidity (Operating)** 20 ~ 95% RH (non-condensing)
- **Humidity (Storage)** 0 ~ 95% RH (non-condensing)
- **Operating Temperature** -10 ~ 70° C
- **Storage Temperature** -20 ~ 80° C