

Incremental encoders

Miniature optical

2400 / 2420 (shaft / hollow shaft)

Push-pull



The incremental miniature encoders type 2400 / 2420 with their optical sensor technology offer a resolution of up to 1024 pulses per revolution.

With a diameter of just 24 mm this encoder is ideal for use where space is tight.













High rotational

Temperature

Shock / vibration resistant

Short-circuit

Magnetic field

Reliable

- · Robust bearing construction.
- · Cable outlet boasts high degree of strain relief thanks to multiple clamping.
- · Short-circuit proof outputs.

Versatile

- · Ideally suited for use in small devices.
- · Meets the certification requirements of railways standard EN 50121.

Order code **Shaft version**





If for each parameter of an encoder the underlined preferred option is selected, then the delivery time will be 10 working days for a Ω ts. up to 50 pcs. of these types generally have a delivery time of 15 working days.



a Flange

1 = ø 24 mm [0.94"]

 $3 = \emptyset 28 \text{ mm } [1.10"]$

 $2 = \emptyset 30 \text{ mm} [1.18"]$

Shaft (ø x L)

 $1 = \emptyset 4 \times 10 \text{ mm} [0.16 \times 0.39"]$

 $3 = \emptyset 5 \times 10 \text{ mm} [0.20 \times 0.39]$, with flat

 $2 = \emptyset 6 \times 10 \text{ mm} [0.24 \times 0.39"]$

 $4 = \emptyset 1/4$ " x 10 mm [1/4" x 0.39"], with flat 1)

 $6 = \emptyset 6 \times 10 \text{ mm} [0.24 \times 0.39^{\circ}], \text{ with flat}^{1)}$

Output circuit / power supply

1 = push-pull (without inverted signal) / 5 ... 24 V DC

2 = push-pull (with inverted signal) / 5 ... 24 V DC

3 = push-pull (without inverted signal) / 8 ... 30 V DC

4 = push-pull (with inverted signal) / 8 ... 30 V DC

Type of connection

1 = axial cable, 2 m [6.56'] PVC

A = axial cable, special length PVC *)

2 = radial cable, 2 m [6.56'] PVC

B = radial cable, special length PVC *)

*) Available special lengths (connection types A, B): 3, 5, 8, 10, 15 m [9.84, 16.40, 26.25, 32.80, 49.21'] order code expansion .XXXX = length in dm ex.: 05.2400.122A.1024.0030 (for cable length 3 m)

Pulse rate

4, 6, 8, 10, 16, 20, 25, 36, 40, 50, 60, 80, 100, 120, 125, 180, 200, 250, 300, 360, 400, 500, 512, 1000, 1024 (e.g. 360 pulses => 0360)

Stock types

05.2400.1122.0050

05.2400.1122.0360

05.2400.1122.0500 05.2400.1122.1000

05.2400.1122.1024

Optional on request - other pulse rates



Incremental encoders

Miniature optical

2400 / 2420 (shaft / hollow shaft)

Push-pull

Order code Hollow shaft

 $\begin{array}{c|c} \textbf{05.2420} & . & \textbf{1} & \textbf{X} & \textbf{X} & . & \textbf{XXXX} \\ \textbf{Type} & \textbf{0} & \textbf{0} & \textbf{0} & . & \textbf{XXXX} \end{array}$

If for each parameter of an encoder the <u>underlined preferred option</u> is selected, then the delivery time will be 10 working days for a maximum of 10 pieces.

Qts. up to 50 pcs. of these types generally have a delivery time of 15 working days.



a Flange

1 = ø 24 mm [0.94"]

b Blind hollow shaft (insertion depth max. 14 mm [0.55"])

1 = ø 4 mm [0.16"] 2 = ø 6 mm [0.24"]

 $4 = \emptyset \ 1/4'' \ 1)$

Output circuit / power supply

1 = push-pull (without inverted signal) / 5 ... 24 V DC

- 2 = push-pull (with inverted signal) / 5 ... 24 V DC
- 3 = push-pull (without inverted signal) / 8 ... 30 V DC
- 4 = push-pull (with inverted signal) / 8 ... 30 V DC
- d Type of connection

1 = axial cable, 2 m [6.56'] PVC

- A = axial cable, special length PVC *)
- 2 = radial cable, 2 m [6.56'] PVC
- B = radial cable, special length PVC *)
- *) Available special lengths (connection types A, B): 3, 5, 8, 10, 15 m [9.84, 16.40, 26.25, 32.80, 49.21'] order code expansion .XXXX = length in dm ex.: 05.2420.122A.1024.0030 (for cable length 3 m)

Pulse rate

4, 6, 8, 10, 16, 20, 25, 36, 40, 50, 60, 80, **100**, 120, 125, 180, 200, 250, 300, **360**, 400, 500, **512**, **1000**, **1024** (e.g. 360 pulses => 0360)

Stock types 05.2420.1212.0500 05.2420.1222.0500 05.2420.1222.1000 05.2420.1222.1024

Optional on request - other pulse rates

Mounting accessory for shaft encoders

Order no.

Coupling

bellows coupling ø 15 mm [0.59"] for shaft 4 mm [0.16"]

Electrical characteristics

8.0000.1202.0404

Further accessories can be found in the accessories section or in the accessories area of our website at: www.kuebler.com/accessories.

Additional connectors can be found in the connection technology section or in the connection technology area of our website at: www.kuebler.com/connection_technology.

Technical data

Mechanical chara	cteristics	
Maximum speed		12000 min ⁻¹
Mass moment of inert	ia	approx. 0.1 x 10 ⁻⁶ kgm ²
Starting torque – at 20	°C [68°F]	< 0.01 Nm ⁴⁾
Shaft load capacity	radial	10 N
	axial	20 N
Weight		approx. 0.06 kg [2.12 oz]
Protection acc. to EN	60529	
	housing side	IP65
	flange side	IP50 (IP64 on request)
Working temperature	range	-20°C +85°C [-4°F +185°F]
Materials	shaft	stainless steel
	blind hollow shaft	brass
Shock resistance acc	to EN 60068-2-27	1000 m/s², 6 ms
Vibration resistance ad	c. to EN 60068-2-6	100 m/s ² , 55 2000 Hz

Output circuit		Push-pull ²⁾ (7272 compatible)	Push-pull ²⁾ (7272 compatible)		
Power supply		5 24 V DC ³⁾	8 30 V DC		
Power consumption	Power consumption (no load)		max. 50 mA		
Permissible load / c	Permissible load / channel		max. +/- 50 mA		
Pulse frequency	Pulse frequency		max. 160 kHz		
Signal level	HIGH	min. +V - 2.5 V	min. +V - 3.0 V		
	LOW	max. 0.5 V	max. 0.5 V		
Rising edge time t _r		max. 1 μs	max. 1 μs		
Falling edge time t _f		max. 1 μs	max. 1 μs		
Short circuit proof outputs		yes	yes		
UL approval		file 224618			
CE compliant acc. to)	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU			

An independent test laboratory (TTI-P-G115/96-01) approved by the German Accreditation Council (DAR) certified the compliance with the Railways Standard, according to EN 50121. This means our encoder is compatible with higher electromagnetic noise standards than standard industrial encoders.

You will have a higher quality encoder even in applications with higher EMC noise levels. We will gladly send you a copy of the test report on request. When ordering an encoder to the railway standard, please ensure you state this explicitly on the order.



¹⁾ US version

Max. recommended cable length 30 m [98.4'].

³⁾ With 24 V DC there is no tolerance above 24 V DC. Please use output circuit 8 ... 30 V DC.

Also for protection level IP64 on the shaft.



Incremental encoders

Miniature 2400 / 2420 (shaft / hollow shaft) **Push-pull** optical

Terminal assignment

Output circuit	Type of connection	Cable (isolate unused wires individually before initial start-up)						
1, 3	1, 2, A, B	Signal:	0 V	+V	Α	В	0	
without inv. signal	1, 2, A, B	Cable color:	WH	BN	GN	YE	GY	

Output circuit	Type of connection	Cable (isolate unused wires individually before initial start-up)								
2, 4	1, 2, A, B	Signal:	0 V	+V	Α	Ā	В	B	0	0
with inv. signal	1, Z, A, B	Cable color:	WH	BN	GN	YE	GY	PK	BU	RD

+V: Encoder power supply +V DC

0 V: Encoder power supply ground GND (0 V)

A, \overline{A} : Incremental output channel A B, \overline{B} : Incremental output channel B

0, $\overline{0}$: Reference signal

Dimensions shaft version

Flange type 1, ø 24 [0.94]

1 min R50 [1.97]

2 3 x M3, 4 [0.16] deep

D	Fit	L
4 [0.16]	f7	10 [0.39]
5 [0.20]	f7	10 [0.39]
6 [0.24]	f7	10 [0.39]
1/Δ"	f7	10 [0 39]


Flange type 2, ø 30 [1.18] Flange type 3, ø 28 [1.10]


1 min R50 [1.97]


2 x M3, 4 [0.16] deep

D	Fit	L
4 [0.16]	f7	10 [0.39]
5 [0.20]	f7	10 [0.39]
6 [0.24]	f7	10 [0.39]
1/4"	f7	10 [0.39]

Flange type	А	В
2	ø 30 [1.18]	3 [0.12]
3	ø 28 [1.10]	2 [0.08]







Dimensions hollow shaft version

Dimensions in mm [inch]

Flange type 1, ø 24 [0.94]

1 4 x M3 DIN 915 - SW1.5

D	Fit	L		
4 [0.16]	H7	14 [0.55]		
6 [0.24]	H7	14 [0.55]		
1/4"	14 [0.55]			
I - insertion denth may blind hollow shaft				

