# **USB-4718**

## 8-channel Thermocouple Input USB Module



### **Features**

- Supports USB 2.0
- Support voltage, current, and thermocouple inputs
- No need for the external power
- 8 thermocouple input channels
- 2,500 V<sub>DC</sub> isolation
- Supports 4~20 mA
- Wiring terminal on modules
- 8-ch isolated DI and 8-ch isolated DO

## Introduction

The USB-4700 series consists of true Plug & Play data acquisition devices. No more opening up your computer chassis to install boards-just plug in the module, then get the data. It's easy and efficient. USB4718 offers 8 thermocouple inputs with 16-bit resolution, up to 0.1% input range accuracy, or 4~20 mA inputs.

Reliable and rugged enough for industrial applications, yet inexpensive enough for home projects, the USB-4718 is the perfect way to add measurement and control capability to any USB capable computer. The USB-4718 is fully USB plug and play and easy to use. It obtains all required power from the USB port, so no external power connection is ever required.

# **Specifications**

#### **Analog Input**

Accuracy ±0.1% for voltage input Bandwidth 13.1 Hz @ 50 Hz, 15.72 Hz @ 60 Hz Channels Eight differential

• Ch. Independent Conf. Yes CMR @ 50/60 Hz 92 dB min. Resolution 16 bits Input Impedance  $20~\mathrm{M}\Omega$ 

 Input Range 0~15 mV, 0~50 mV, 0~100 mV, 0~500 mV,

0~1 V, 0~2.5 V, 0~20 mA, 4~20 mA

Input Types Thermocouple, mV, V, mA Sampling Rate 10 samples/sec. (total) Span Drift ±25 ppm/° C

T/C Type and Temperature Ranges

| J | 0 ~ 760° C    | R | 500 ~1750° C |
|---|---------------|---|--------------|
| K | 0 ~ 1370° C   | S | 500 ~1750° C |
| T | -100 ~ 400° C | В | 500 ~1800° C |
| E | 0 ~ 1000° C   |   |              |

 TVS/ESD Protection Built-in Zero Drift ±3 μV/° C

#### **Isolated Digital Input**

Channels

Logic 0: 2 V max. Input Voltage

Logic 1: 5 V min. (30 V max.)

 Isolation Protection 2,500 V<sub>DC</sub> ■ Opto-Isolator Response 25 µs

#### **Isolated Digital Output**

Channels Sink (NPN) **Output Type** 

**Isolation Protection** 

 $2,500 \text{ V}_{DC}$ 5 ~ 30 V<sub>DC</sub>, 1.1 A max/total **Output Voltage** Sink Current 200 mA max./channel

Opto-isolator Response 25 µs

#### General

Bus Type USB 2.0

I/O Connector On board screw terminal Dimensions (LxWxH): 132 x 80 x 32 mm **Power Consumption** 0.1 A @ 5 V **Power Input** 5 V from USB line **Watchdog Timer** 1.6 sec. (system)

**Operating Temperature**  $0 \sim 60^{\circ}$  C (32  $\sim 140^{\circ}$  F) (refer to IEC 68-2-1, 2)

Storing Temperature -20 ~ 70° C (-4 ~ 158° F)

- Storing Humidity 5 ~ 95% RH non-condensing (refer to IEC 68-2-3)

## **Ordering Information**

USB-4718 8-channel Thermocouple Input USB Module, CD,

manual and one 1.8m USB 2.0 cable included

**ADVANTECH** Last updated: 20-Jan-2006