

BG GHDE HO SA UL PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

General ordering data

Type	BG GHDE HO SA UL PT6
Order No.	1113120000
Version	FieldPower® Box, IP 65 with corresponding housing, Polycarbonate, GF 10
GTIN (EAN)	4032248891887
Qty.	1 pc(s).

BG GHDE HO SA UL PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 684 g

Temperatures

Operating temperature	-40 °C...+45 °C	Storage temperature	-40 °C...+80 °C
Temperature range, installation, min.	10 °C	Temperature range, installation, max.	40 °C

General information #96 connectors

UL 94 flammability rating 5VA

General specifications

Halogen	No	Insulating material	Polycarbonate, GF 10
Protection degree	IP 65 with corresponding housing	Silicone	No
Colour	Black	UL 94 flammability rating	5VA
Cover attachment	Slotted/Phillips screws	Torque for cover screws	2 Nm

Technical data Switch

Clamping range, plug, max.	10 mm ²	Clamping range, plug, min.	0.75 mm ²
Operating voltage	440 V	Plug standards	IEC 60947-3
Pollution severity	3	Power rating AC-23A	7.5 kW
Rated current AC-23A	16 A	Switch type	ABB OT16ET3
Terminals - torque	0.8 N-m	Wire connection cross section AWG, max.	AWG 18
Wire connection cross section AWG, min.	AWG 8	auxiliary contact	ABB OA1G10

Classifications

ETIM 3.0	EC000216	eClass 6.2	27-37-14-03
eClass 7.1	27-37-14-03		