

## RSM-Series RSM 16RS 115VUC LP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



Clip-on RS 30. 31. 32 relay bases are available in widths from 11.2 to 25 mm, depending on the type.  
 The RSM relay multiplexers are available as 4, 8 and 16-way modules. To reduce the wiring work, the DC variants are fitted with a common plus or minus potential.  
 The optional IEC603-1 plug-in connector enables the connection of pre-assembled lines.  
 The screw connection system is used to connect the conductor with a rated cross-section of 2.5 mm<sup>2</sup>.

### General ordering data

Type	RSM 16RS 115VUC LP
Order No.	<a href="#">1114761001</a>
Version	RSM-Series, Relays, No. of contacts: 1, CO contact, AgNi 90/10, Rated control voltage: 115 V AC / DC, Continuous current: 6 A, Screw connection
GTIN (EAN)	4032248047864
Qty.	1 pc(s).

## RSM-Series RSM 16RS 115VUC LP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	285 mm	Height	87 mm
Depth	76 mm	Net weight	676 g

### Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature	-25 °C...+50 °C
Storage temperature	-40 °C...+60 °C		

### Input

Coil resistance		Pull-inrop-out current, typ.	
Rated control voltage	115 V AC / DC	Rated current DC	6 A
Power rating	0.6 VA	Pull-inrop-out typ.	
Status indicator	LED yellow		

### Output

Max. switching voltage, AC	250 V	Continuous current	6 A
Inrush current	8 A	Max. switching power	2000 VA
Switch-on delay	≤ 8msdc/10msac	Switch-off delay	≤ 5msdc/8msac
Duration of Bounce	≤ 3 ms	Min. switching power	250 mW
Max. switching frequency at rated load	0.1 Hz		

### Contact data

No. of contacts	1	Contact design	CO contact
Contact material	AgNi 90/10	Mechanical service life	30 x 10 <sup>6</sup> switching cycles
Electrical service life of AC coil	> 7x10 <sup>3</sup> Switching cycles	Electrical service life, DC coil	> 5x10 <sup>5</sup> switching cycles

### General data

Wire connection method	Screw connection	Humidity	40 °C / 93 % rel. humidity, no condensation
Wire cross-section, solid, max.	2.5 mm <sup>2</sup>		

### Insulation coordination

Creepage and clearance distance input – output	> 3 mm	Rated voltage	250 V
Impulse withstand voltage	4 kV	Protection degree	IP 20
Pollution severity	2	Surge voltage category	III

### Other technical data

Version	Relay coupler	Status indicator	LED yellow
---------	---------------	------------------	------------

### Further details of approvals / standards

Standards	DIN EN 50178
-----------	--------------

**Datenblatt**

**RSM-Series  
RSM 16RS 115VUC LP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Connection data**

Clamping range, rated connection	2.5 mm <sup>2</sup>	Clamping range, rated connection, max.	4 mm <sup>2</sup>
Clamping range, rated connection, min.	0.5 mm <sup>2</sup>	Stripping length, rated connection	8 mm
Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>
Wire connection method	Screw connection	Wire cross-section, solid, max.	2.5 mm <sup>2</sup>
Wire cross-section, solid, min.	0.5 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC001437	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-01	eClass 6.2	27-37-16-01
eClass 7.1	27-37-16-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Declaration of Conformity [K34\\_05\\_10.pdf](#)