

**RSM PLC
RSM-8 PLC C 1CO S**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Digital output interface per-relay for electrical signal transmission between the PLC and the field.

- Electrical isolation using pluggable relays.
- Integrated LED status display.
- Screw or tension clamp connection.
- The relay switchover can be carried out by the PLC or manually by a relay.
- Two available versions: compact (RSS Relais) or standard (RSS Relais) .

General ordering data

Type	RSM-8 PLC C 1CO S
Order No.	1128970000
Version	Interface, RSM PLC, 8, RSS, Screw connection
GTIN (EAN)	4032248910366
Qty.	1 pc(s).

RSM PLC RSM-8 PLC C 1CO S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	75 mm	Width	109 mm
Height	85 mm	Net weight	305 g

Temperatures

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

General data

LED status display per relay	green	Fuse per relay	No
LED status of the supply voltage	yellow	Power supply fuse	2.5 A

Connection data

Connection on control side	Connector according IEC60603-13/DIN41651	Number of poles (control side)	20-pole plug
Connection (field side)	LP2N 5.08mm	Connection supply	LP 5.08mm

Rating data

Mechanical service life	5 x 10 ⁶ switching cycles
-------------------------	--------------------------------------

Ratings data input

Input voltage	24 V DC ± 10%	Input current	13 mA
Power rating	0.36 W		

Ratings data output

Relay type	RSS	Type of output	Potential-free contact
Contact material	AgNi 90/10	Rated voltage (text)	250 V AC
Max. AC continuous current	2.5 A	Minimum contact current	0.1 A
Minimum contact voltage	5 V		

Insulation coordinates (EN50178)

According to	DIN EN 50178	Rated input insulation voltage	< 50 V AC
Rated output insulation voltage	250 V AC	Overvoltage category input/output	III
Overvoltage category input/output	II	Overvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	≥ 5.5 mm
Clearance input/output	≥ 0.2 mm	Clearance output/output	≥ 1.17 mm

Connection field

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	0.5 mm ²	Sleeve with plastic collar, max.	2.5 mm ²
Min. wire cross-section, AWG [field]	AWG 26	Max. wire cross-section, AWG [field]	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Erstellungs-Datum December 17, 2013 10:27:01 AM CET

RSM PLC RSM-8 PLC C 1CO S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	2.5 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Classifications

eClass 6.2	27-37-16-01	eClass 7.1	27-37-16-01
------------	-------------	------------	-------------

Product information

Descriptive text accessories	Relay 4060120000 RSS 24 V DC 1CO
------------------------------	----------------------------------

Approvals

Approvals



ROHS	Conform
------	---------

RSM PLC
RSM-8 PLC C 1CO S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

