Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Plug component, Nominal current: 41 A, Rated voltage (III/2): 1000 V, Number of positions: 8, Pitch: 7.62 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Product Features

- Unlimited 600 V UL approval
- CP-PC coding profile as protection against mismatching
- Maximum contact reliability due to integrated double steel spring
- Automatic, tool-free snap-lock mechanism using the Click and Lock system (-STCL); high level of safety even in the event of vibrations
- High-capacity plugs with a current carrying capacity of 41 A and a connection capacity of 6 mm², stranded/10 mm², solid

Key commercial data

package_quantity	50
GTIN	4046356523035

Technical data

Dimensions

Length	35.5 mm
Height	19.7 mm
Pitch	7.62 mm
Dimension a	53.34 mm

General

Range of articles	PC 5/..-STF1
Insulating material group	I
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Nominal current I_N	41 A
Nominal cross section	6 mm²
Maximum load current	41 A
Insulating material	PA

Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

Technical data

General

Inflammability class according to UL 94	V0
Internal cylindrical gage	A4
Stripping length	10 mm
Number of positions	8
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.8 Nm

Connection data

Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	10 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	6 mm²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm²
Conductor cross section stranded, with ferrule without plastic sleeve max.	6 mm²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
2 conductors with same cross section, solid min.	0.2 mm²
2 conductors with same cross section, solid max.	2.5 mm²
2 conductors with same cross section, stranded min.	0.2 mm²
2 conductors with same cross section, stranded max.	4 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.25 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm²
Minimum AWG according to UL/CUL	24
Maximum AWG according to UL/CUL	8

classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190

Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

classifications

eCl@ss

eCl@ss 6.0	27261101
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	41 A	41 A
mm²/AWG/kcmil	24-8	24-8

cUL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	41 A	41 A
mm²/AWG/kcmil	24-8	24-8

GOST

Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

approvals

cULus Recognized

accessories

Screwdriver tools

SZK PH1 VDE - 1205150



SZS 0,6X3,5 - 1205053



Coding element


CP-PC RD - 1701967



Drawings


Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

Diagram



Derating curve for: PC 5/...-ST1-7,62 with PC 4/....-G-7,62Conductor cross section: 4 mm²


Diagram



Derating curve for: PC 5/...-ST1-7,62 with PC 5/...-G-7,62Conductor cross section: 6 mm²

Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

Diagram




Derating curve for: PC 5/...-ST1-7,62 with PC 5/...-G-7,62Conductor cross section: 10 mm²

Diagram

Type: PC 5/...-STF1-7,62 with PCVK 4-7,62 and PCVK 4-7,62-F


Diagram



Type: PC 5/...-ST(F)1-7,62 with PC 5/...-GU(F)-7,62 Conductor cross section: 6 mm²


Printed-circuit board connector - PC 5/ 8-STF1-7,62 - 1777891

Diagram



Type: PC 5/...-ST(F)1-7,62 with PC 5/...-G(F)U-7,62 Conductor cross section: 10 mm²

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com