


**RS ELCO  
RS ELCO 56/54RM S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



ELCO contacts inserts are used in electrical power plants, refineries and a variety of process applications – wherever stable and reliable signal transmission is required. The ELCO connector features both a reliable connection system and a high signal capacity.

The line of RS ELCO interfaces and pre-assembled PAC ELCO cables is a specially designed solution for these requirements.

**General ordering data**

Type	RS ELCO 56/54RM S
Order No.	<a href="#">1126730000</a>
GTIN (EAN)	4032248908264
Qty.	1 pc(s).

**RS ELCO  
RS ELCO 56/54RM S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	155 mm	Width	70 mm
Height	60 mm	Net weight	175 g

**Temperatures**

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

**Connection Data**

Connection on control side	ELCO plug-in connector	Number of poles (control side)	56-pole plug
Contact material (control side)	Phosphor bronze alloy	Polarity hardware codification	1
Connector alignment	Right	Connection (field side)	LP2N 5.08mm
Number of poles (field side)	54 P		

**Rating data**

Rated voltage	150 V AC / 200 V DC	Rated current per connection	1.5 A
Total operating current	81 A		

**Insulation coordination (EN50178)**

According to	DIN EN 50178	Rated insulation voltage	< 150 V AC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.5 kV	Insulation test voltage	0.8 kVAC

**Connection field**

Type of connection	Screw connection	Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	6 mm <sup>2</sup>	Solid, min. H05(07) V-U	0.5 mm <sup>2</sup>
Solid, max. H05(07) V-U	6 mm <sup>2</sup>	Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>
Flexible, max. H05(07) V-K	4 mm <sup>2</sup>	Flexible with sleeve, max.	2.5 mm <sup>2</sup>
Flexible with sleeve, min.	0.5 mm <sup>2</sup>	Sleeve with plastic collar, max.	2.5 mm <sup>2</sup>
Min. wire cross-section, AWG [field]	AWG 26	Max. wire cross-section, AWG [field]	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

**Classifications**

eClass 6.2	27-24-22-04	eClass 7.1	27-24-22-04
------------	-------------	------------	-------------

**Product information**

Descriptive text technical data	Polarizer in position 1
Descriptive text accessories	Refer to the "Universal cables PAC-ELCO" section in this chapter

**Approvals**

Approvals



ROHS Conform

## Datenblatt

**RS ELCO**  
**RS ELCO 56/54RM S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Downloads

PDF

[Table of connections](#)

**Datenblatt**

**RS ELCO  
RS ELCO 56/54RM S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

