


**RS ELCO
RS ELCO 90/90LM Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



ELCO contacts inserts are used in electrical power plants, refineries and a variety of process applications – wherever stable and reliable signal transmission is required. The ELCO connector features both a reliable connection system and a high signal capacity.

The line of RS ELCO interfaces and pre-assembled PAC ELCO cables is a specially designed solution for these requirements.

General ordering data

Type	RS ELCO 90/90LM Z
Order No.	1126880000
GTIN (EAN)	4032248908523
Qty.	1 pc(s).

RS ELCO RS ELCO 90/90LM Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	242 mm	Width	109 mm
Height	76 mm	Net weight	420 g

Temperatures

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

Connection Data

Connection on control side	ELCO plug-in connector	Number of poles (control side)	90-pole plug
Contact material (control side)	Phosphor bronze alloy	Polarity hardware codification	1
Connector alignment	Left	Connection (field side)	LM2NZF 5.08mm
Number of poles (field side)	90 P		

Rating data

Rated voltage	150 V AC / 200 V DC	Rated current per connection	0.5 A
Total operating current	45 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 150 V AC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.5 kV	Insulation test voltage	0.8 kVAC

Connection field

Type of connection	Tension clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Sleeve with plastic collar, max.	1.5 mm ²
Min. wire cross-section, AWG [field]	AWG 24	Max. wire cross-section, AWG [field]	AWG 14
Stripping length	7.5 mm		

Classifications

eClass 6.2	27-24-22-04	eClass 7.1	27-24-22-04
------------	-------------	------------	-------------

Product information

Descriptive text technical data	Polarizer in position 1
Descriptive text accessories	Refer to the "Universal cables PAC-ELCO" section in this chapter

Approvals

Approvals



ROHS Conform

Datenblatt

RS ELCO
RS ELCO 90/90LM Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Downloads

PDF

[Table of connections](#)

Datenblatt

**RS ELCO
RS ELCO 90/90LM Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

