

**FAD
FAD S7/300 HE20 UNIV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Front adapters for Siemens S7-300 20- and 40-pole cards. The power can be supplied directly to the front adapter and it can be commonly or individually distributed per byte (8 signals).

General ordering data

Type	FAD S7/300 HE20 UNIV
Order No.	1127840000
Version	Interface, FAD, All-purpose, Connector according IEC60603-13/DIN41651 20 p
GTIN (EAN)	4032248909261
Qty.	1 pc(s).

Datenblatt

**FAD
FAD S7/300 HE20 UNIV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	124 mm	Width	23 mm
Net weight	20 g		

Temperatures

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

Connection data

Connection (field side)	Connector according IEC60603-13/DIN41651 20 p	Connection to PLC	Siemens S7-300
Connection to the card	Siemens S7-300 card with 20-pole connector and operating voltage of ≤ 30 VAC / 60 VDC		

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Total operating current	20 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	0.5 kV	Insulation test voltage	0.35 kVAC

Classifications

eClass 6.2	27-24-22-04	eClass 7.1	27-24-22-04
------------	-------------	------------	-------------

Approvals

Approvals



ROHS Conform

Datenblatt

FAD
FAD S7/300 HE20 UNIV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

