


**RS VERT
RS VERT 4P 20X4 Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Distributor module with 4 voltage potentials (P1,P2,P3,P4) in 20P1,20P2,20P3 and 20P4 for tension-clamp or screw connection.

General ordering data

Type	RS VERT 4P 20X4 Z
Order No.	1128110000
Version	Interface, RS VERT, 4 P, Tension clamp connection
GTIN (EAN)	4032248909650
Qty.	1 pc(s).

RS VERT RS VERT 4P 20X4 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	145 mm	Width	70 mm
Height	52 mm	Net weight	311 g

Temperatures

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

Connection data

Number of potentials	4	Distribution PCB connectors	LM2NZF 5.08mm
Supply plug-in connectors	TOP 1.5GS2/180		

Rating data

Rated voltage (text)	< 600 V AC	Maximum current per potential connection	30 A
Maximum current per distributor connection	15 A	Total operating current	120 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 600 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	6 kV	Insulation test voltage	1.65 kVAC

Connection field

Type of connection	Tension clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Sleeve with plastic collar, max.	1.5 mm ²
Min. wire cross-section, AWG [field]	AWG 24	Max. wire cross-section, AWG [field]	AWG 14
Stripping length	7.5 mm		

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	4 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	4 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 10
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	13 mm		

Classifications

eClass 6.2	27-24-22-04	eClass 7.1	27-24-22-04
------------	-------------	------------	-------------

Datenblatt

**RS VERT
RS VERT 4P 20X4 Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform

Datenblatt

**RS VERT
RS VERT 4P 20X4 Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

