

MH KTB MH 403020 S4E3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Stainless steel enclosures for use in areas exposed to explosion hazards

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing bolt welded in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

Type	KTB MH 403020 S4E3
Order No.	1194980000
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 400 mm, 300 mm, 200 mm
GTIN (EAN)	4032248977710
Qty.	1 pc(s).

MH KTB MH 403020 S4E3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	200 mm	Width	300 mm
Height	400 mm	Depth	200 mm
Mounting dimension - width	356 mm	Mounting dimension - height	247 mm
Net weight	10,400 g		

Cable glands, left

M12 (3)	48	M16 (3)	32
M20 (3)	20	M25 (3)	17
M32 (3)	9	M40 (3)	7
M50 (3)	3	M63 (3)	3
M75 (3)	2		

Cable glands, right

M12 (2)	48	M16 (2)	32
M20 (2)	20	M25 (2)	17
M32 (2)	9	M40 (2)	7
M50 (2)	3	M63 (2)	3
M75 (2)	2		

Cable glands, top/bottom

M12	38	M16	26
M20	17	M25	14
M32	7	M40	6
M50	3	M63	2
M75	2		

General information

AF size 1	10 mm	Access opening: height	347 mm
Access opening: width	241 mm	Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
Gland plates	Bottom, left, right	Installation advice	Terminal rail / mounting plate
Material thickness	1.5 mm	Material thickness of cover	1.5 mm
Material thickness of flange	3 mm	Max. payload	48 kg
Opening angle lid	125 °	Overall dimensions	411 x 381 x 215
Position PE bolts	Page C	Material	Stainless steel 1.4404 (316L)
Seal material	Silicone	Surface finish	electropolished
Operating temperature, min.	-60 °C	Operating temperature, max.	135 °C
Impact resistance	7 J ATEX version, 10 J version standard	Protection degree	IP 66, IP 67
Note: protection class	For use in the temperature range over 105°C, the IP protection is limited to IP 66.	Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross- shaped feet)
Cover attachment	4 hinges and M6 hex-head slotted screws SW10	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread

MH
KTB MH 403020 S4E3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

WDU 10 ZDU 10	2x21	WDU 16 ZDU 16	2x18
WDU 2,5 ZDU 2,5 IDU 2,5	3x42	WDU 35 ZDU 35	1x13
WDU 4 ZDU 4	3x35	WDU 6 ZDU 6	2x26

vertical assembly

WDU 10 ZDU 10 (2)	1x32	WDU 16 ZDU 16 (2)	1x26
WDU 2,5 ZDU 2,5 IDU 2,5 (2)	2x62	WDU 35 ZDU 35 (2)	1x20
WDU 4 ZDU 4 (2)	2x52	WDU 6 ZDU 6 (2)	1x39

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0046U	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0015U	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

Product information

Descriptive text ordering data Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data *For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.
 Recommended order:
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal) ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

Approvals

Approvals



ROHS Conform

**MH
KTB MH 403020 S4E3**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Zeichnungen

