


**RSF PLC
RSF PLC 2W 32IO LEDS Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Compact interfaces for transmitting 32 digital input/output signals (RSF SPS).

- Signals optionally with byte grouping (can be set using jumper).
- Can be switched between positive or negative signal (set with jumper)
- An optional LED status display shows the status and the operating voltages.
- Each circuit can be protected by 5x20 mm individual fuses.
- Available with tension-clamp or screw connection.

General ordering data

Type	RSF PLC 2W 32IO LEDS Z
Order No.	1128210000
Version	Interface, RSF PLC, LED, 2-wire, Tension clamp connection
GTIN (EAN)	4032248909766
Qty.	1 pc(s).

RSF PLC RSF PLC 2W 32IO LEDS Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	170 mm	Width	87 mm
Height	72 mm	Net weight	115 g

Temperatures

Operating temperature	-25...+50°C	Storage temperature	-40...+60 °C
-----------------------	-------------	---------------------	--------------

General data

LED status display per channel	Green (negative -) / red (positive +)	Fuse per channel	No
LED status of the supply voltage	yellow	Power supply fuse	2.5 A
Default setting	Shared minus connection		

Connection data

Connection on control side	Connector according IEC60603-13/DIN41651	Number of poles (control side)	40-pole plug
Connection (field side)	LM2NZF 5.08mm	Connection supply	LM2NZF 5.08mm
Wiring system	2-wire		

Ratings data

Operating voltage	24 V DC \pm 10%	Max. current for common pole	3 A
Max. current per channel	1 A	Max. current per byte	2 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50 μ s)	0.5 kV	Insulation test voltage	0.35 kVAC

Connection field

Type of connection	Tension clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Sleeve with plastic collar, max.	1.5 mm ²
Min. wire cross-section, AWG [field]	AWG 24	Max. wire cross-section, AWG [field]	AWG 14
Stripping length	7.5 mm		

Supply connection

Type of connection	Tension clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Ferrule with plastic collar, max.	1.5 mm ²
Wire cross-section, min. AWG	AWG 24	Wire cross-section, max. AWG	AWG 14
Stripping length	7.5 mm		

Classifications

eClass 6.2	27-24-22-04	eClass 7.1	27-24-22-04
------------	-------------	------------	-------------

Erstellungs-Datum December 17, 2013 10:26:54 AM CET

Datenblatt**RSF PLC
RSF PLC 2W 32IO LEDS Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Product information**

Descriptive text technical data Factory setting: Common negative pole

Approvals

Approvals



ROHS Conform

Downloads

PDF [Instruction Manual](#)

**RSF PLC
RSF PLC 2W 32IO Leds Z**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

