

MH KTB MH 484815 S4E3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Stainless steel enclosures for use in areas exposed to explosion hazards

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing bolt welded in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

Type	KTB MH 484815 S4E3
Order No.	1195130000
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 480 mm, 480 mm, 150 mm
GTIN (EAN)	4032248977772
Qty.	1 pc(s).

MH KTB MH 484815 S4E3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	150 mm	Width	480 mm
Height	480 mm	Depth	150 mm
Mounting dimension - width	536 mm	Mounting dimension - height	327 mm
Net weight	15,200 g		

Cable glands, left

M12 (3)	36	M16 (3)	20
M20 (3)	17	M25 (3)	7
M32 (3)	6	M40 (3)	5
M50 (3)	4	M63 (3)	0
M75 (3)	0		

Cable glands, right

M12 (2)	36	M16 (2)	20
M20 (2)	17	M25 (2)	7
M32 (2)	6	M40 (2)	5
M50 (2)	4	M63 (2)	0
M75 (2)	0		

Cable glands, top/bottom

M12	39	M16	22
M20	19	M25	8
M32	7	M40	6
M50	5	M63	0
M75	0		

General information

AF size 1	10 mm	Access opening: height	427 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
	421 mm	Installation advice	Terminal rail / mounting plate
Gland plates	Bottom, left, right	Material thickness of cover	1.5 mm
Material thickness	1.5 mm	Max. payload	92 kg
Material thickness of flange	3 mm	Overall dimensions	491 x 561 x 165
Opening angle lid	125 °	Material	Stainless steel 1.4404 (316L)
Position PE bolts	Page C	Surface finish	electropolished
Seal material	Silicone	Operating temperature, max.	135 °C
Operating temperature, min.	-60 °C	Protection degree	IP 66, IP 67
Impact resistance	7 J ATEX version, 10 J version standard	Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross- shaped feet)
Note: protection class	For use in the temperature range over 105°C, the IP protection is limited to IP 66.	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread
Cover attachment	4 hinges and M6 hex-head slotted screws SW10		

MH
KTB MH 484815 S4E3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

WDU 10 ZDU 10	3x39	WDU 16 ZDU 16	2x32
WDU 2,5 ZDU 2,5 IDU 2,5	4x77	WDU 35 ZDU 35	2x24
WDU 4 ZDU 4	3x64	WDU 6 ZDU 6	3x48

vertical assembly

WDU 10 ZDU 10 (2)	2x39	WDU 16 ZDU 16 (2)	2x33
WDU 2,5 ZDU 2,5 IDU 2,5 (2)	4x78	WDU 35 ZDU 35 (2)	1x25
WDU 4 ZDU 4 (2)	3x65	WDU 6 ZDU 6 (2)	3x49

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0046U	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0015U	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

Product information

Descriptive text ordering data Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data *For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.
 Recommended order:
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal) ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

Approvals

Approvals



MH
KTB MH 484815 S4E3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Zeichnungen

