

**QL
KTB QL 221513 S4E4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Stainless steel enclosures for use in areas exposed to explosion hazards**

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB QL enclosure range offers further improvements to a product line that is already successfully leading the market.

General ordering data

| | |
|------------|--|
| Type | KTB QL 221513 S4E4 |
| Order No. | 1199890000 |
| Version | Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 229 mm, 152 mm, 133 mm |
| GTIN (EAN) | 4032248982639 |
| Qty. | 1 pc(s). |

QL KTB QL 221513 S4E4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|----------------------------|-----------|-----------------------------|--------|
| Length | 133 mm | Width | 152 mm |
| Height | 229 mm | Depth | 133 mm |
| Mounting dimension - width | 208 mm | Mounting dimension - height | 152 mm |
| Net weight | 4,579.2 g | | |

Cable glands, left

| | | | |
|---------|---|---------|---|
| M12 (3) | 8 | M16 (3) | 6 |
| M20 (3) | 3 | M25 (3) | 2 |
| M32 (3) | 2 | M40 (3) | 2 |
| M50 (3) | 0 | M63 (3) | 0 |
| M75 (3) | 0 | | |

Cable glands, right

| | | | |
|---------|---|---------|---|
| M12 (2) | 8 | M16 (2) | 6 |
| M20 (2) | 3 | M25 (2) | 2 |
| M32 (2) | 2 | M40 (2) | 2 |
| M50 (2) | 0 | M63 (2) | 0 |
| M75 (2) | 0 | | |

Cable glands, top/bottom

| | | | |
|-----|---|-----|---|
| M12 | 6 | M16 | 5 |
| M20 | 2 | M25 | 2 |
| M32 | 1 | M40 | 1 |
| M50 | 0 | M63 | 0 |
| M75 | 0 | | |

General information

| | | | |
|------------------------------|---|-----------------------------|---|
| AF size 1 | 10 mm | Access opening: height | 176 mm |
| Access opening: width | 93 mm | Areas of use | Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore |
| Gland plates | Bottom, top, left, right | Installation advice | Terminal rail / mounting plate |
| Material thickness | 1.5 mm | Material thickness of cover | 1.5 mm |
| Material thickness of flange | 3 mm | Max. payload | 14 kg |
| Opening angle lid | 125 ° | Overall dimensions | 251 x 233 x 143 |
| Position PE bolts | Page C | Material | Stainless steel 1.4404 (316L) |
| Seal material | Silicone | Surface finish | electropolished |
| Operating temperature, min. | -60 °C | Operating temperature, max. | 135 °C |
| Impact resistance | 7 J ATEX version, 10 J version standard | Protection degree | IP 66 |
| Enclosure attachment | 4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross-shaped feet) | Cover attachment | Quarter-turn fastener with slotted insert |
| Integral fixing | 4, 6 or 9 stud bolts M6 inner (female) thread | | |

Datenblatt

QL
KTB QL 221513 S4E4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

| | | | |
|-------------------------|------|---------------|------|
| WDU 10 ZDU 10 | 1x7 | WDU 16 ZDU 16 | 1x6 |
| WDU 2,5 ZDU 2,5 IDU 2,5 | 1x15 | WDU 4 ZDU 4 | 1x13 |
| WDU 6 ZDU 6 | 1x9 | | |

vertical assembly

WDU 2,5 ZDU 2,5 IDU 2,5 (2) 1x29

Classifications

eClass 6.2 27-14-91-07 eClass 7.1 27-14-91-07

Test certificates

| | | | |
|-------------------------|-----------------|-----------------------------|--------------|
| Certificate No. (ATEX) | KEMA10ATEX0051 | Certificate No. (GERMLLOYD) | 11534-10 |
| Certificate No. (IECEX) | IECEXKEM10.0020 | Certificate No. (MARITREG) | 10.04095.250 |
| Certificate no. (cULus) | E243298VOL1SEC5 | | |

Product information

Descriptive text ordering data Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data *For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.
 Recommended order:
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal)
 ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

Approvals

Approvals



QL
KTB QL 221513 S4E4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

