

**Industrial Ethernet
IE-C5ES8VG0030M40M40-G**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled cables, patch cable Cabinet Line, Cat. 5, PVC,
green

General ordering data

Type	IE-C5ES8VG0030M40M40-G
Order No.	1166020030
Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/ IEC 11801), PVC, 3 m
GTIN (EAN)	4032248956845
Qty.	1 pc(s).

Industrial Ethernet IE-C5ES8VG0030M40M40-G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	3 m	Net weight	140 g
--------	-----	------------	-------

Temperatures

Operating temperature	-40 °C...+75 °C	Storage temperature	
Installation temperature			

Electrical properties

Insulation resistance	5000 MΩ	Operating voltage	100 V
PoE PoE+	conforming to IEEE 802.3at		

Standards

Generic communication cable facilities	ISO / IEC 11801:2002, EN 50173-1:2007	Connector standard	IEC 60603-7-51
Standard, assembly		Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)
	UL-Style 2879 (80°C/30V)		
Standard, wire material	DIN EN 13602 Cu-ETP-A	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B

Cable structure

Wire material	Stranded tin-plated copper wire	Standard designations	LI02YSCY 4X2X0.15 PIMF GN, SF/UTP
Strands	7	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm ²
Insulation	PE	Insulation cross-section	0.98 mm
Wire core insulation thickness	0.25 mm	No. of wires	8
Arrangement of wire cores	Twisted pair	Diameter of wire pair	2.4 mm
Wire pair shielding		Colour sequence or wires - wire pairs	white/blue - blue, white/orange - orange, white/green - green, white/brown - brown
	Aluminium foil, Plastic foil		
Shielding	S/FTP	Complete shielding	Shielding braid made from copper wiring
Shielding braid thickness	0.1 mm	Overlap of shielding braid	70 %
Material sheath	PVC	Sheath diameter, min.	6 mm
Sheath diameter, max.	6.4 mm	Sheathing material thickness	0.5 mm
Sheathing colour	green (RAL 6018)		

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801)	Operating voltage	100 V
Operating voltage, UL	30 V	Test voltage: wire-wire-shield, at RMS 50Hz, 1 min.	700 V
Characteristic impedance	100 ± 5 Ω at 100MHz	Loop resistance	150 Ω/km
Deviation	25 ns/100m	Resistance differential	3 %
Transfer impedance	15 mΩ/m at 1 MHz, 20 mΩ/m at 10 MHz, 30 mΩ/m at 30 MHz	Shield attenuation	55 dB at 30–600 MHz
Insulation resistance	5000 MΩ	Capacity at 1 kHz	48 nF/km
Signal propagation time	5.13 ns/m		

Industrial Ethernet IE-C5ES8VG0030M40M40-G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Mechanical and material properties of cable

Min. bending radius, once only	5 *diameter	Min. bending radius, repetitive	10 *diameter
Abrasion resistance	good	Resistance to spread of flame	in accordance with IEC 60332-1

plug

Version connector left	RJ45 IP 20	Version connector right	RJ45 IP 20
------------------------	------------	-------------------------	------------

Classifications

ETIM 3.0	EC001262	UNSPSC	26-12-16-06
eClass 5.1	27-06-18-02	eClass 6.2	27-06-03-90
eClass 7.1	27-06-18-01		

Approvals

ROHS	Conform
------	---------

Industrial Ethernet IE-C5ES8VG0030M40M40-G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Wiring

RJ45	1	white, orange	1	RJ45
	2	orange	2	
	3	white, green	3	
	4	blue	4	
	5	white, blue	5	
	6	green	6	
	7	white, brown	7	
	8	brown	8	