

**QL
KTB QL 624520 S4E2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Stainless steel enclosures for use in areas exposed to explosion hazards**

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB QL enclosure range offers further improvements to a product line that is already successfully leading the market.

General ordering data

Type	KTB QL 624520 S4E2
Order No.	1200740000
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 620 mm, 450 mm, 200 mm
GTIN (EAN)	4032248982967
Qty.	1 pc(s).

QL KTB QL 624520 S4E2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	200 mm	Width	450 mm
Height	620 mm	Depth	200 mm
Mounting dimension - width	476 mm	Mounting dimension - height	450 mm
Net weight	15,830 g		

Cable glands, left

M12 (3)	80	M16 (3)	54
M20 (3)	36	M25 (3)	30
M32 (3)	17	M40 (3)	14
M50 (3)	6	M63 (3)	5
M75 (3)	4		

Cable glands, right

M12 (2)	80	M16 (2)	54
M20 (2)	36	M25 (2)	30
M32 (2)	17	M40 (2)	14
M50 (2)	6	M63 (2)	5
M75 (2)	4		

Cable glands, top/bottom

M12	63	M16	42
M20	27	M25	23
M32	12	M40	10
M50	4	M63	4
M75	3		

General information

AF size 1	10 mm	Access opening: height	567 mm
Access opening: width	391 mm	Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
Gland plates	Bottom, top	Installation advice	Terminal rail / mounting plate
Material thickness	1.5 mm	Material thickness of cover	1.5 mm
Material thickness of flange	3 mm	Max. payload	112 kg
Opening angle lid	125 °	Overall dimensions	642 x 501 x 210
Position PE bolts	Page C	Material	Stainless steel 1.4404 (316L)
Seal material	Silicone	Surface finish	electropolished
Operating temperature, min.	-60 °C	Operating temperature, max.	135 °C
Impact resistance	7 J ATEX version, 10 J version standard	Protection degree	IP 66
Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross-shaped feet)	Cover attachment	Quarter-turn fastener with slotted insert
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread		

QL
KTB QL 624520 S4E2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

WDU 10 ZDU 10	4x36	WDU 16 ZDU 16	3x30
WDU 2,5 ZDU 2,5 IDU 2,5	5x71	WDU 35 ZDU 35	2x22
WDU 4 ZDU 4	5x59	WDU 6 ZDU 6	4x45

vertical assembly

WDU 10 ZDU 10 (2)	2x53	WDU 16 ZDU 16 (2)	2x44
WDU 2,5 ZDU 2,5 IDU 2,5 (2)	3x105	WDU 35 ZDU 35 (2)	1x33
WDU 4 ZDU 4 (2)	3x88	WDU 6 ZDU 6 (2)	3x66

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0051	Certificate No. (GERMLLOYD)	11534-10
Certificate No. (IECEX)	IECEXKEM10.0020	Certificate no. (cULus)	E243298VOL1SEC5

Product information

Descriptive text ordering data Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data *For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.
 Recommended order:
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal)
 ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

Approvals

Approvals



