

**MH
KTB MH 453815 S4E1****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Stainless steel enclosures for use in areas exposed to explosion hazards**

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing bolt welded in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

Type	KTB MH 453815 S4E1
Order No.	1195010000
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 458 mm, 382 mm, 150 mm
GTIN (EAN)	4032248977857
Qty.	1 pc(s).

MH KTB MH 453815 S4E1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	150 mm	Width	382 mm
Height	458 mm	Depth	150 mm
Mounting dimension - width	408 mm	Mounting dimension - height	305 mm
Net weight	9,000 g		

Cable glands, left

M12 (3)	33	M16 (3)	19
M20 (3)	16	M25 (3)	7
M32 (3)	6	M40 (3)	5
M50 (3)	4	M63 (3)	0
M75 (3)	0		

Cable glands, right

M12 (2)	33	M16 (2)	19
M20 (2)	16	M25 (2)	7
M32 (2)	6	M40 (2)	5
M50 (2)	4	M63 (2)	0
M75 (2)	0		

Cable glands, top/bottom

M12	30	M16	17
M20	15	M25	6
M32	5	M40	4
M50	4	M63	0
M75	0		

General information

AF size 1	10 mm	Access opening: height	405 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
Gland plates	323 mm	Installation advice	Terminal rail / mounting plate
Material thickness	Bottom	Material thickness of cover	1.5 mm
Material thickness of flange	1.5 mm	Max. payload	70 kg
Opening angle lid	3 mm	Overall dimensions	469 x 433 x 165
Position PE bolts	125 °	Material	Stainless steel 1.4404 (316L)
Seal material	Page C	Surface finish	electropolished
Operating temperature, min.	Silicone	Operating temperature, max.	135 °C
Impact resistance	-60 °C	Protection degree	IP 66, IP 67
Note: protection class	7 J ATEX version, 10 J version standard	Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross- shaped feet)
Cover attachment	For use in the temperature range over 105°C, the IP protection is limited to IP 66.	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread

MH
KTB MH 453815 S4E1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Housing earth

Earth, housing, internal Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

horizontal assembly

WDU 10 ZDU 10	2x29	WDU 16 ZDU 16	2x24
WDU 2,5 ZDU 2,5 IDU 2,5	4x58	WDU 35 ZDU 35	1x18
WDU 4 ZDU 4	3x48	WDU 6 ZDU 6	3x36

vertical assembly

WDU 10 ZDU 10 (2)	2x37	WDU 16 ZDU 16 (2)	2x31
WDU 2,5 ZDU 2,5 IDU 2,5 (2)	3x73	WDU 35 ZDU 35 (2)	1x23
WDU 4 ZDU 4 (2)	2x62	WDU 6 ZDU 6 (2)	2x46

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0050	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0019	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

Product information

Descriptive text ordering data Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data *For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.
 Recommended order:
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal) ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

Approvals

Approvals



**MH
KTB MH 453815 S4E1**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Zeichnungen

