

## MH KTB MH 553520 S4E2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### Stainless steel enclosures for use in areas exposed to explosion hazards

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries.

The new Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing bolt welded in the cover and base of the enclosure
- Welded mounting feet
- International approvals

### General ordering data

Type	KTB MH 553520 S4E2
Order No.	<a href="#">1195270000</a>
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 550 mm, 350 mm, 200 mm
GTIN (EAN)	4032248978229
Qty.	1 pc(s).

## MH KTB MH 553520 S4E2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	200 mm	Width	350 mm
Height	550 mm	Depth	200 mm
Mounting dimension - width	376 mm	Mounting dimension - height	350 mm
Net weight	11,500 g		

### Cable glands, left

M12 (3)	70	M16 (3)	48
M20 (3)	30	M25 (3)	26
M32 (3)	14	M40 (3)	12
M50 (3)	5	M63 (3)	4
M75 (3)	3		

### Cable glands, right

M12 (2)	70	M16 (2)	48
M20 (2)	30	M25 (2)	26
M32 (2)	14	M40 (2)	12
M50 (2)	5	M63 (2)	4
M75 (2)	3		

### Cable glands, top/bottom

M12	45	M16	30
M20	20	M25	17
M32	9	M40	7
M50	3	M63	3
M75	2		

### General information

AF size 1	10 mm	Access opening: height	497 mm
Access opening: width	291 mm	Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
Gland plates	Bottom, top	Installation advice	Terminal rail / mounting plate
Material thickness	1.5 mm	Material thickness of cover	1.5 mm
Material thickness of flange	3 mm	Max. payload	77 kg
Opening angle lid	125 °	Overall dimensions	572 x 401 x 215
Position PE bolts	Page C	Material	Stainless steel 1.4404 (316L)
Seal material	Silicone	Surface finish	electropolished
Operating temperature, min.	-60 °C	Operating temperature, max.	135 °C
Impact resistance	7 J ATEX version, 10 J version standard	Protection degree	IP 66, IP 67
Note: protection class	For use in the temperature range over 105°C, the IP protection is limited to IP 66.	Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross-shaped feet)
Cover attachment	4 hinges and M6 hex-head slotted screws SW10	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread

**Datenblatt**

**MH  
KTB MH 553520 S4E2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten**

**Housing earth**

Earth, housing, internal      Welded-on M6 stainless-steel earth stud in lower part of housing and lid.

**horizontal assembly**

WDU 10 ZDU 10	3x26	WDU 16 ZDU 16	3x22
WDU 2,5 ZDU 2,5 IDU 2,5	4x52	WDU 35 ZDU 35	2x16
WDU 4 ZDU 4	4x43	WDU 6 ZDU 6	4x32

**vertical assembly**

WDU 10 ZDU 10 (2)	2x46	WDU 16 ZDU 16 (2)	1x39
WDU 2,5 ZDU 2,5 IDU 2,5 (2)	2x91	WDU 35 ZDU 35 (2)	1x29
WDU 4 ZDU 4 (2)	2x76	WDU 6 ZDU 6 (2)	2x58

**Classifications**

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

**Test certificates**

Certificate No. (ATEX)	KEMA10ATEX0050	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0019	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

**Product information**

Descriptive text ordering data      Colour variations may possibly occur in the case of painted housings.

Descriptive text technical data      \*For enclosure versions with zero, one or two gland plates, the horizontal gap between the mounting feet is reduced by 30 mm.  
 Assembly with terminal blocks provides for 10 mm clearance to the ends of the mounting rail.  
 Recommended order:  
 TS 35 mounting rail (screw terminal) WDU 2.5 1020000000 / (tension clamp terminal) ZDU 2.5 1608510000 / (tension clamp terminal) PDU 2.5 1896110000  
 TS 32 mounting rail (screw terminal) SAK 2.5 0279660000  
 TS 15 mounting rail (screw terminal) AKZ 2.5 0697160000

**Approvals**

Approvals



**MH**  
**KTB MH 53520 S4E2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Zeichnungen**

