

**Industrial Ethernet
IE-SFP-1GSXLC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- IEEE 802.3z-compliant (Gigabit modules)
- IEEE 802.3u-compliant (Fast Ethernet modules)
- Symmetric LVPECL I/Os (Gigabit modules)
- Symmetric PECL I/Os (Fast Ethernet modules)
- TTL signal detection indicator
- In operation insertable duplex LC connector
- Class 1 laser product, EN60825-1 compliant
- -40 to 85°C operating temperature (T models)

General ordering data

Type	IE-SFP-1GSXLC
Order No.	1241490000
Version	SFP-Modul, 0 °C...+60 °C, Gigabit-Ethernet, Multimode, LC connectors, 500 m
GTIN (EAN)	4050118029512
Qty.	1 pc(s).

Industrial Ethernet IE-SFP-1GSXLC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 25 g

EMC conformity and approvals

Security UL, TÜV

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	0 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic Gigabit Ethernet

Link budget Gigabit Ethernet	8.5 dB	Max. TX Gigabit Ethernet	-4 dBm
Min. TX Gigabit Ethernet	-9.5 dBm	Receive sensitivity Gigabit Ethernet	-18 dBm
System reserve Gigabit Ethernet	0 dBm	Typical distances Gigabit Ethernet	550 m (50/125 µm or 62.5/125 µm, 400 MHz * km at 850 nm multi-mode fibre optic cable)
Wave length Gigabit Ethernet	850 nm		

Guarantee

Time interval 3 years

Interfaces

Ethernet ports 1 Plug-in connector Duplex-LC

Order data

Operating temperature	SFP alternatives	Gigabit-Ethernet, Multimode, LC connectors, 500 m
0 °C...+60 °C		

Classifications

eClass 6.2 19-17-01-06 eClass 7.1 19-17-01-06

Approvals

Approvals



ROHS Conform

Downloads

Declaration of Conformity [K4230912.pdf](#)