

SAIL-M8BG-4S3.0UIE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

Type	SAIL-M8BG-4S3.0UIE
Order No.	1301370300
Version	Bus line, One end without connector, M8, No. of poles: 4, 3 m, Female socket, straight, shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4050118111224
Qty.	1 pc(s).

SAIL-M8BG-4S3.OUIE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 127 g

Technical specifications for cable

No. of poles shielded	4 Yes	Core cross-section	0.15 mm ²
Colour coding	Blue, Orange, white / blue, white / orange	Insulation	PP
Sheathing colour	Green	Sheath material	PUR
Cable length	3 m	Outer diameter	4.8 - 0.3 mm
Temperature range, stationary, max.	80 °C	Temperature range, stationary, min.	-40 °C
Suitable for cable carriers	Yes	Halogen	No
Bending radius, min., stationary	4 x cable diameter	Torsion resistance	0 °/m
Acceleration	5 m/s ²	Bending radius, min., moving	7.5 x cable diameter
Bending cycles	5 Mio	Speed	180 m/min
		Resistant to welding beads	No

General technical data

Version	Female socket, straight	Contact tube diameter	M8
Housing main material	PUR	Threaded ring material	Brass, nickel-plated
Coding	none	Protection degree	IP 67
Contact surface	Gold-plated	LED	No
Rated voltage	30 V	Rated current	4 A
Insulation resistance	10 ⁸ Ω	Temperature range of housing	-25...+80 °C
Tightening torque	M8: 0.5 - 0.6 Nm	Plugging cycles	≥ 100
Pollution severity	3	jumpered	No

Classifications

eClass 6.2 27-27-92-18 eClass 7.1 27-27-92-18

Approvals


ROHS Conform

SAIL-M8BG-4S3.OUIE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com


Zeichnungen

Dimensioned drawing



Pin

Pole scheme



Socket

Circuit diagram

The ideal tool, the Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F