

**Industrial Ethernet
IE-FM6C2UE0100MSD1SD1X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

General ordering data

Type	IE-FM6C2UE0100MSD1SD1X
Order No.	1318011000
Version	Dragline cable, SC IP 67 bayonet V01 metal, SC IP 67 bayonet V01 metal, 62.5 µm, PUR, 100 m
GTIN (EAN)	4050118127515
Qty.	1 pc(s).

Industrial Ethernet IE-FM6C2UE0100MSD1SD1X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	100 m	Net weight	5,300 g
--------	-------	------------	---------

Temperatures

Operating temperature	-40 °C...+85 °C	Storage temperature	-55 °C...+85 °C
Installation temperature	-55 °C...+60 °C		

Fibre-optic

Attenuation	2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm	Bandwidth	200 MHz*km at 850 nm, 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM1	Insertion loss	≤ 0.4 dB
Return loss (attenuation)	≥ 30 dB		

Cable structure

Core diameter	62.5 µm	Sheath diameter	7.5–8 mm
Cable layout	Break-out dragline	Material sheath	PUR
Sheathing colour	Black		

Mechanical and material properties of cable

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	70 mm		

plug

Version connector left	SC IP 67 bayonet V01 metal	Version connector right	SC IP 67 bayonet V01 metal
------------------------	-------------------------------	-------------------------	-------------------------------

Classifications

ETIM 3.0	EC000034	eClass 5.1	27-06-18-03
eClass 6.2	27-06-18-03	eClass 7.1	27-06-18-03

Approvals

ROHS	Conform
------	---------

Datenblatt

**Industrial Ethernet
IE-FM6C2UE0100MSD1SD1X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Detailed drawing

