

HDC kits

HDC-KIT-HE 06.101

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.

Screw connection

General ordering data

Type	HDC-KIT-HE 06.101
Order No.	1712660000
Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Size: 3, Poles: 6, Screw connection, 500 V, 24 A, diecast aluminium, PG 16
GTIN (EAN)	4008 190947897
Qty.	1 pc(s).

**HDC kits
HDC-KIT-HE 06.101**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 388.68 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General data

Cable glands	PG 16	Connection type PE	Screw connection
Material	diecast aluminium	No. of poles	6
Rated current (DIN EN 61984)	24 A	Rated voltage (DIN EN 61984)	500 V
Series	HE	Size	3

Version

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Material	diecast aluminium	Max. torque for main contact	0.55 Nm
Min. torque for main contact	0.5 Nm	Size	3
Surface finish	Powder coating	Type of connection	Screw connection

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC002943
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-07-03	eClass 7.1	27-44-05-15
eClass 8.1	27-44-05-15	eClass 9.0	27-44-02-92
eClass 9.1	27-44-01-90		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN, WSCAD