## ANNOUNCED SPECIFICATION OF HS-5645MG STANDARD SPORT DIGITAL HIGH TORQUE SERVO

1.TECHNICAL VALUES

CONTROL SYSTEM

OPERATING VOLTAGE RANGE

**OPERATING TEMPERATURE RANGE** 

**TEST VOLTAGE** 

OPERATING SPEED STALL TORQUE

OPERATING ANGLE

DIRECTION

**IDLE CURRENT** 

**RUNNING CURRENT** 

DEAD BAND WIDTH

CONNECTOR WIRE LENGTH

DIMENSIONS WEIGHT :+PULSE WIDTH CONTROL 1500usec NEUTRAL

:4.8V TO 6.0V

:-20 TO +60° C

:AT 4.8V :AT 6.0V

:0.23sec/60° AT NO LOAD :0.18sec/60° AT NO LOAD

:10.3kg.cm(143.03oz.in) :12.1kg.cm(168.03oz.in)

:45°/ONE SIDE PULSE TRAVELING 400usec

:CLOCK WISE/PULSE TRAVELING 1500 TO 1900usec


:3mA :3mA :450mA

:1usec

:300mm(11.81in)

:40.6x19.8x37.8mm(1.59x0.77x1.48in)

:60g(2.11oz)



## 2.FEATURES

**DIGITAL & MOS FET AMP** 

**PROGRAMABLE** 

3-POLE FERRITE MOTOR

**DUAL BALL BEARING** 

3-METAL GEARS

LONG LIFE POTENTIOMETER

## 3.APPLICATIONS

AIRCRAFT TO 1/4 SCALE 30 TO 60 SIZE HELICOPTERS

STEERING AND THROTTLE FOR 1/10TH & 1/8TH ON-ROAD AND OFF-ROAD VEHICLES