

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name** **REVELL EMAIL COLOR transparent**
Nr. 730; Nr. 731; Nr. 752
- **Article number:**
Dreisol:
R3280-0730; R3280-0731; R3280-0752
REVELL.:
32730; 32731; 32752;
- **UFI:** 1J10-906G-000U-RTNU
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use** SU21 Consumer uses: Private households / general public / consumers
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category** PROC10 Roller application or brushing
- **Application of the substance / the mixture** toy lacquer
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Dreisol Coatings GmbH & Co.KG. Tel.: +49(0)5742-9300-0(Zentrale)
Industriestraße 4 Fax : +49(0)5742-9300-49
D-32361 Pr. Oldendorf-Bad Holzhausen E-Mail: mail@dreisol.de
<http://www.dreisol.de>
- Revell GmbH
Henschelstr. 20-30 Tel.: +49(0)5223-965-0
D-32257 Bünde <http://www.revell.de>
- **Informing department:**
department product safety Tel.: +49(0)5742/9300-41
e-mail adress of competent person: sdb@dreisol.de
- **1.4 Emergency telephone number:** Poison Information Centre (GIZ-Nord): Tel.: +49(0)551-19240

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



GHS07

STOT SE 3 H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 1)

· **Hazard pictograms**

GHS02 GHS07

· **Signal word** Warning· **Hazard-determining components of labelling:**

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*

· **Hazard statements**

H226 Flammable liquid and vapour.

H336 May cause drowsiness or dizziness.

· **Precautionary statements**

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P240 Ground/bond container and receiving equipment.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Additional information:**

EUH066 Repeated exposure may cause skin dryness or cracking.

· **Labelling of packages where the contents do not exceed 125 ml**· **Hazard pictograms**

GHS02 GHS07

· **Signal word** Warning· **Hazard-determining components of labelling:**

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*

· **Hazard statements**

H336 May cause drowsiness or dizziness.

· **Precautionary statements**

P102 Keep out of reach of children.

· **Information pertaining to particular dangers for man and environment**· **Additional information**

Child-resistant fastening not required (Annex II, Part 3.1 CLP)

Tactile warning not required (Annex II, Part 3.2 CLP)

SECTION 3: Composition/information on ingredients· **3.2 Chemical characterisation: Mixtures**· **Description:**

Paint mixture based on acryl-copolymer and/or pigment/extender with the following components.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 2)

· Dangerous components:

CAS: 1174522-20-3 EC number: 919-857-5 Reg.nr.: 01-2119463258-33	Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics* Flam. Liq. 3, H226 Asp. Tox. 1, H304 STOT SE 3, H336	25-50%
CAS: 107-98-2 EINECS: 203-539-1 Reg.nr.: 01-2119457435-35	1-methoxypropan-2-ol Flam. Liq. 3, H226 STOT SE 3, H336	12.5-20%
CAS: 108-65-6 EINECS: 203-603-9 Reg.nr.: 01-2119475791-29	2-methoxy-1-methylethyl acetate Flam. Liq. 3, H226	1-2%

· Additional information

*) Benzene content is less than 0.1% (EINECS-No. 200-753-7). It is P. Note
 Contains no other ingredients (≅ 0,1%) that are classified as hazardous to health or the environment according to the current knowledge of the supplier and must be mentioned in this section.
 The wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

· 4.1 Description of first aid measures

- **General information** Remove contaminated, saturated clothing immediately.
- **After inhalation**
 Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.
 In case of unconsciousness bring patient into stable side position for transport.
- **After skin contact**
 Instantly wash with water and soap and rinse thoroughly.
 If skin irritation continues, consult a doctor.
- **After eye contact**
 Rinse opened eye for several minutes under running water. If symptoms persist, consult doctor.
- **After swallowing** Do not induce vomiting; instantly call for medical help.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents** CO₂, sand, extinguishing powder. Do not use water.
- **For safety reasons unsuitable extinguishing agents** Water.
- **5.2 Special hazards arising from the substance or mixture**
 Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazards.
- **5.3 Advice for firefighters**
- **Protective equipment:** Wear self-contained breathing apparatus.
- **Additional information**
 Cool closed containers exposed to fire with water.
 Do not allow run-off from fire fighting to enter drains or water courses.

GB

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 3)

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Remove all sources of ignition. Provide adequate ventilation. Refer to protective measurer, listed in sections 7 and 8.
- **6.2 Environmental precautions:**
Do not allow product to enter into sewerage systems or water bodies.
Inform respective authorities in case of product reaches water or sewage systems.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **6.4 Reference to other sections**
See Section 7 for information on safe handling
See Section 8 for information on personal protection equipment.
See Section 13 for information on disposal.

* **SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at working place.
Keep containers tightly sealed.
- **Information about protection against explosions and fires:**
Protect against electrostatic charges.
Keep ignition sources away - Do not smoke.
Vapours are heavier than air and may spread along floors. Vapours may form explosive mixture with air.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by warehouses and containers:** Store only in the original container.
- **Information about storage in one common storage facility:**
Keep away from foodstuffs, beverages and food.
- **Further information about storage conditions:** Protect from heat and direct sunlight.
- **Storage class 3**
- **7.3 Specific end use(s)** No further relevant information available.

* **SECTION 8: Exposure controls/personal protection**

- **Additional information about design of technical systems:**
Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.

· **8.1 Control parameters**

- **Components with critical values that require monitoring at the workplace:**

107-98-2 1-methoxypropan-2-ol

WEL (Great Britain)	Short-term value: 560 mg/m ³ , 150 ppm Long-term value: 375 mg/m ³ , 100 ppm Sk
IOELV (European Union)	Short-term value: 568 mg/m ³ , 150 ppm Long-term value: 375 mg/m ³ , 100 ppm Skin

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 4)

108-65-6 2-methoxy-1-methylethyl acetate

WEL (Great Britain)	Short-term value: 548 mg/m ³ , 100 ppm Long-term value: 274 mg/m ³ , 50 ppm Sk
IOELV (European Union)	Short-term value: 550 mg/m ³ , 100 ppm Long-term value: 275 mg/m ³ , 50 ppm Skin

· DNELs

1174522-20-3 Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*

Oral	DNEL	300 mg/kg/day (General population, long-term exposure)
Dermal	DNEL	300 mg/kg/day (General population, long-term exposure) 300 mg/kg/day (Workers, long-term exposure)
Inhalative	DNEL	900 mg/m ³ (General population, long-term exposure) 1,500 mg/m ³ (Workers, long-term exposure)

107-98-2 1-methoxypropan-2-ol

Oral	DNEL	3.3 mg/kg/day (General population, long-term exposure)
Dermal	DNEL	18.1 mg/kg/day (General population, long-term exposure) 50.6 mg/kg/day (Workers, long-term exposure)
Inhalative	DNEL	43.9 mg/m ³ (General population, long-term exposure) 369 mg/m ³ (Workers, long-term exposure) 553.5 mg/m ³ (Workers, short-term exposure)

· PNECs

107-98-2 1-methoxypropan-2-ol

PNEC	100 mg/L (sewage treatment plant) 1 mg/L (marine water) 10 mg/L (freshwater)
PNEC	2.47 mg/kg (soil) 4.17 mg/kg (sediment (marine water)) 41.6 mg/kg (sediment (freshwater))

· 8.2 Exposure controls

· Personal protective equipment

· General protective and hygienic measures

Instantly remove any spoiled and impregnated garments.

After skin contact clean with water and soap or use appropriate detergents. Do not use organic solvent.

Keep away from foodstuffs, beverages and food.

· Breathing equipment:

In case of brief exposure or low pollution use breathing filter apparatus. In case of intensive or longer exposure use breathing apparatus, independent of circulating air.

Filter A/P2.

· Protection of hands:

The instructions and information provided by the glove manufacturer on use, storage, maintenance and replacement must be followed. Barrier creams may help to protect the exposed areas of the skin.

· Material of gloves

Nitrile rubber or fluorine rubber (0.4 mm). Breakthrough time > 480min with full contact. Notice., The information provided by the glove manufacturer to permeability and breakthrough times and the

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 5)

specific workplace conditions When cracking or change in color, shape or elasticity, the gloves should be changed immediately.

- **Eye protection:** Tightly sealed safety glasses.
- **Body protection:** Protective work clothing.

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Fluid
Colour:	According to product specification
Smell:	Benzen-like
Odour threshold:	Not determined.

· Change in condition

Initial boiling point and boiling range: 119-155 °C

· **Flash point:** 35 °C (DIN/ISO 3679)

· **Inflammability (solid, gaseous)** Not applicable.

· **Ignition temperature:** 200 °C (DIN 51794)

· **Decomposition temperature:** Not determined.

· **Self-inflammability:** Product is not self-igniting.

· **Explosive properties:** Product is not explosive. However, formation of explosive air/steam mixtures is possible.

· Critical values for explosion:

Lower:	0.6 Vol %
Upper:	11.0 Vol %

· **Steam pressure at 20 °C:** 10.8 hPa

· **Density at 20 °C** 0.820-0.920 g/cm³ (DIN 51757)

· **Relative density** Not determined.

· **Vapour density** Not determined.

· **Evaporation rate** Not determined.

· Solubility in / Miscibility with

Water: Not miscible or difficult to mix

· Viscosity:

dynamic: Not determined.

kinematic at 20 °C: 60 s (DIN 53211/4)

· **or at 20 °C:** 60 s (ISO 2431-1993/6 mm)

· Solvent content:

Organic solvents: 67.3 %

Water: 0.0 %

VOC (EG) 580 g/l

Solids content: 30.0 %

(Contd. on page 7)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 6)

· **9.2 Other information**

The values of specific gravity and viscosity are an orienting information.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:**
 Strong oxidizing agent.
 Strong acids and bases
- **10.6 Hazardous decomposition products:**
 such as carbon monoxide and dioxide, smoke, oxides of nitrogen etc.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity**
 There are no data available on the preparation itself.
 The mixture is classified under Regulation No 1272/2008 = CLP (EU-GHS) Regulation and the toxicological hazards. See Section 3 and 15 for details.

· **LD/LC50 values that are relevant for classification:**

1174522-20-3 Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*

Oral	LD50	>15,000 mg/kg (rat (Ratte))
Dermal	LD50	>3,000 mg/kg (kan)

107-98-2 1-methoxypropan-2-ol

Oral	LD50	>5,000 mg/kg (rat (Ratte))
Dermal	LD50	13,500 mg/kg (rabbit (Kaninchen))
Inhalative	LC50/4 h	25 mg/l (rat (Ratte))

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Other observations:**
 Exposure to component solvents vapours concentration in excess of the stated occupational exposure limit may result in adverse health effect such as mucous membrane and respiratory system irritation and adverse effect on kidney, liver and central nervous system.
 Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases, loss of consciousness.
 Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin resulting in non-allergic contact dermatitis and absorption through the skin. Repeated or prolonged skin contact may lead to allergic contact dermatitis.
 The liquid splashed in the eyes may cause irritation and reversible damage.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
 May cause drowsiness or dizziness.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 7)

- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

1174522-20-3 Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*

EC50/72h >1,000 mg/l (algae)

LC/EC50 (72 h) >1,000 mg/l (Onchorhynchus mykiss (Regenbogenforelle))

107-98-2 1-methoxypropan-2-ol

LC50/96h >4,000 mg/l (Leuciscus idus(Goldorfe)) (Fische)

20,800 mg/l (Pimephales promelas (Elritze)) (Fische)

EC50/48h >100 mg/l (wfl) (Daphnien)

LC/EC50 (72 h) >100 mg/l (algae, different)

· **12.2 Persistence and degradability** No further relevant information available.

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **Additional ecological information:**

· **General notes:**

Water hazard class 1 (Self-assessment): slightly hazardous for water.

Do not allow undiluted product or large quantities of it to reach ground water, water bodies or sewage system.

· **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed of together with household garbage. Do not allow product to enter into sewage systems.

Hand over to disposers of hazardous waste.

· **European waste catalogue**

The waste key numbers are not only product separating essentially application-oriented. The waste key number valid for the application can be taken from the European waste catalogue.

Refer to Community provisions relating to waste in Europe. Note that national or regional provisions may be in force.

· **Uncleaned packagings:**

· **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, ADN, IMDG**

Void

· **IATA**

UN1263

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31


Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 8)

<ul style="list-style-type: none"> · 14.2 UN proper shipping name · ADR, ADN, IMDG · IATA 	<p>Void PAINT</p>
<ul style="list-style-type: none"> · 14.3 Transport hazard class(es) · ADR, ADN, IMDG · Class · IATA 	<p>Void</p>
<div style="text-align: center;">  </div> <ul style="list-style-type: none"> · Class · Label 	<p>3 Flammable liquids. 3</p>
<ul style="list-style-type: none"> · 14.4 Packing group · ADR, IMDG · IATA 	<p>Void III</p>
<ul style="list-style-type: none"> · 14.5 Environmental hazards: · Marine pollutant: 	<p>No</p>
<ul style="list-style-type: none"> · 14.6 Special precautions for user 	<p>Not applicable.</p>
<ul style="list-style-type: none"> · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code 	<p>Not applicable.</p>
<ul style="list-style-type: none"> · Transport/Additional information: · ADR · Remarks: · Transport in accordance with ADR/RID, IMDG and ICAO/IATA. 	<p>> 450 ltr.: UN-1263 PAINT, 3, III, (D/E)</p>
<ul style="list-style-type: none"> · IMDG · Remarks: 	<p>> 30 ltr.: UN-1263 PAINT, 3, III</p>
<ul style="list-style-type: none"> · UN "Model Regulation": 	<p>Void</p>

SECTION 15: Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- Directive 2012/18/EU
- Named dangerous substances - ANNEX I None of the ingredients is listed.
- Seveso category P5c FLAMMABLE LIQUIDS
- Qualifying quantity (tonnes) for the application of lower-tier requirements 5.000 t
- Qualifying quantity (tonnes) for the application of upper-tier requirements 50.000 t
- REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- National regulations
- Water hazard class: Water hazard class 1 (Self-assessment): slightly hazardous for water.
- VOC value EC %: <66.33 %

(Contd. on page 10)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 03.02.2020

version: 17

Revision: 03.02.2020

Trade name REVELL EMAIL COLOR transparent
Nr. 730; Nr. 731; Nr. 752

(Contd. of page 9)

- **Switzerland VOC value:** 67.13 %
- **VOC (EU)** <600.2 g/l
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

The information of this SDS is based on the present state of our knowledge and on current EU and national laws. The product is not to be used for other purposes than those specified under section 1 without first obtaining written handling instruction. It is always the responsibility of the user to take all necessary steps in order to fulfil the demand laid down in the local rules and legislation. The information in this SDS is meant as a description of the safety requirements of our product : it is not to be considered as a guarantee of the products' properties.

· **Relevant phrases**

Danger notes of the contents substances listed under item 3.

H226 Flammable liquid and vapour.

H304 May be fatal if swallowed and enters airways.

H336 May cause drowsiness or dizziness.

· **Classification according to Regulation (EC) No 1272/2008**

Physical hazard: Flash point (° C)

Health and environmental hazards: calculation method

· **Department issuing data specification sheet:** department product safety

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

Flam. Liq. 3: Flammable liquids – Category 3

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Asp. Tox. 1: Aspiration hazard – Category 1

· *** Data compared to the previous version altered.**

Paragraphs, which were changed compared to the former version, are marked with "*" on the left margin.