





MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque				
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm				
SF10-16160N-38HRACB	6,0-15,0	14,8	24.000	0,15	20.110	0,77	3,18	6,69	4,00	19,60	12,40	3	none	carbon



DIRECTION OF ROTATION



UNIT: MILLIMETER



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted