

SAIB-VSA-4P/250/9-OB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

General ordering data

Type	SAIB-VSA-4P/250/9-OB
Order No.	1873080000
Version	Valve plug, Socket, angled
GTIN (EAN)	4032248495351
Qty.	1 pc(s).

SAIB-VSA-4P/250/9-OB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	26 g
------------	------

Temperatures

Operating temperature range, max.	85 °C	Operating temperature range, min.	-25 °C
Operating temperature, max.	85 °C	Operating temperature, min.	-25 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits		Cable diameter, max.	
	Without circuitry		8 mm
Cable diameter, min.	6 mm	Cable glands	PG 9
Coding	Design A (18 mm)	Connection cross-section, max.	1.5 mm ²
Connection cross-section, min.	0.34 mm ²	Contact surface	Ni
Housing main material	PA 6 GF	Insulation strength	10 ⁸ Ω
No. of poles	4	Pollution severity	3
Protection degree	IP65	Rated current	10 A
Rated voltage	250 V	Temperature range of housing	-25...+85 °C
Type of connection	Screw connection		

Classifications

ETIM 3.0	EC002062	ETIM 4.0	EC002636
ETIM 5.0	EC002636	ETIM 6.0	EC002062
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-01
eClass 6.2	27-26-07-03	eClass 7.1	27-44-01-01
eClass 8.1	27-44-01-01	eClass 9.0	27-44-01-05
eClass 9.1	27-06-03-12		

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
--------------------	---