



Material Safety Data Sheet

1. Product & Company Identification

Product:	Pb rechargeable battery (model CE12V/3,2Ah)
Manufacturer:	Conrad Electronic SE
Nominal voltage:	12 V
Nominal capacity:	3.2 Ah
Address:	Klaus-Conrad-Str. 1, D-92240 Hirschau
Telephone:	+49 (0) 9604 / 40 - 8988
Date of issue:	12.03.2014

2. Hazardous Ingredients / Identity Information

C.A.S.	PRINCIPAL HAZARDOUS COMPONENT(S) (chemical & common name(s))	Hazard Category	% Weight	ACGIH TLV - mg/m ³	OSHA PEL/TWA - mg/m ³
7439-92-1	Lead/Lead Oxide (Litharge)/Lead Sulfate	Acute-Chronic	60-70	0.05 mg/m ³	0.05 mg/m ³
7440-70-2	Calcium (lead calcium alloy)	Reactive	<0.15	Not Established	Not Established
7440-31-5	Tin	Chronic	<1	2	2
7440-38-2	Arsenic (inorganic)	Acute-Chronic	<1	0.01	0.01
7664-93-9	Sulfuric Acid (Battery Electrolyte)	Reactive-Oxidizer Acute -Chronic	10-15	1.0	1.0
Not applicable	Inert Ingredients	Not applicable	<6	Not Applicable	Not Applicable

Note:

PEL's for Individual states may differ from OSHA's PEL's. Check with local authorities for the applicable state PEL's.

OSHA – Occupational Safety and Health Administration; ACGIH – American Conference of Governmental Industrial Hygienists; NIOSH – National Institute for Occupational Safety and Health.

COMMON NAME: (Used on label) Valve Regulated Lead-acid Battery (Trade Name & Synonyms) VRB, VRLA, SLAB, Recombinant lead acid: RG, GPL, AGM, PVX or FD Series, D8565 series

Chemical Family: Toxic and Corrosive Material Mixture

Chemical Name: Battery, Storage, Lead Acid, Valve Regulated

Formula: Lead/Acid



Material Safety Data Sheet

3. Hazard Identification

Signs and Symptoms of Exposure

1. Acute Hazards

Do not open battery. Avoid contact with internal components. Internal components include lead and absorbed electrolyte.

Electrolyte - Electrolyte is corrosive and contact may cause skin irritation and chemical burns. Electrolyte causes severe irritation and burns of eyes, nose and throat. Ingestion can cause severe burns and vomiting.

Lead - Direct skin or eye contact may cause local irritation. Inhalation or ingestion of lead dust or fumes may result in headache, nausea, vomiting, abdominal spasms, fatigue, sleep disturbances, weight loss, anemia and leg, arm and joint pain.

2. Subchronic and Chronic Health Effects

Electrolyte - Repeated contact with electrolyte causes irritation and skin burns. Repeated exposure to mist may cause erosion of teeth, chronic eye irritation and/or chronic inflammation of the nose, throat and lungs.

Lead - Prolonged exposure may cause central nervous system damage, gastrointestinal disturbances, anemia, irritability, metallic taste, insomnia, wrist-drop, kidney dysfunction and reproductive system disturbances. Pregnant women should be protected from excessive exposure to prevent lead from crossing the placental barrier and causing infant neurological disorders.

California Proposition 65 Warning: Battery posts, terminals, and related accessories contain lead and lead compounds, chemicals known to the State of California to cause cancer and reproductive harm, and during charging, strong inorganic acid mists containing sulfuric acid are evolved, a chemical Known to the State of California to cause cancer. Wash hands after handling.

Medical Conditions Generally Aggravated by Exposure

Contact with internal components if battery is broken or opened, then persons with the following medical conditions must take precautions: pulmonary edema, bronchitis, emphysema, dental erosion and tracheobronchitis.

Routes of Entry Inhalation: YES
 Ingestion: YES
 Eye Contact: YES

Chemical(s) Listed as Carcinogen or potential Carcinogen

Proposition 65	YES
National Toxicology Program	YES
I.A.R.C. Monographs	YES
O.S.H.A.	NO



Material Safety Data Sheet

4. First Aid Measured

Emergency and First Aid Procedures	Contact with internal components if battery is opened/broken.
1. Inhalation	Remove to fresh air and provide medical oxygen/CPR if needed. Obtain medical attention.
2. Eyes	Immediately flush with water for at least 15 minutes, hold eyelids open. Obtain medical attention.
3. Skin	Flush contacted area with large amounts of water for at least 15 minutes. Remove contaminated clothing and obtain medical attention if necessary.
4. Ingestion	Do not induce vomiting. If conscious drink large amounts of water/milk. Obtain medical attention. Never give anything by mouth to an unconscious person.

5. Firefighting Measures

Flash Point	Not Applicable
Flammable Limits in Air % by Volume	Not Applicable
Extinguishing Media	Class ABC, CO2, Halon
Auto-Ignition	675°F (polypropylene)

Special Fire Fighting Procedures

Temperature Lead/acid batteries do not burn, or burn with difficulty. Do not use water on fires where molten metal is present. Extinguish fire with agent suitable for surrounding combustible materials. Cool exterior of battery if exposed to fire to prevent rupture. The acid mist and vapors generated by heat or fire are corrosive. Use NIOSH approved self-contained breathing apparatus (SCBA) and full protective equipment operated in positive pressure mode.

Unusual Fire and Explosion Hazards

Sulfuric acid vapors are generated upon overcharge and polypropylene case failure. Use adequate ventilation. Avoid open flames/sparks/other sources of ignition near battery.

6. Accidental Release Measures

Procedures for Cleanup:

Avoid contact with any spilled material. Contain spill, isolate hazard area, and deny entry. Limit site access to emergency responders. Neutralize with sodium bicarbonate, soda ash, lime or other neutralizing agent. Place battery in suitable container for disposal. Dispose of contaminated material in accordance with applicable local, state and federal regulations. Sodium bicarbonate, soda ash, sand, lime or other neutralizing agent should be kept on-site for spill remediation.

Personal Precautions:

Acid resistant aprons, boots and protective clothing. ANSI approved safety glasses with side shields/face shield recommended.

Environmental Precautions:

Lead and its compounds and sulfuric acid can pose a severe threat to the environment. Contamination of water, soil and air should be prevented.



Material Safety Data Sheet

7. Handling and Storage

Precautions to be Taken in Handling and Storage

Store away from reactive materials, open flames and sources of ignition as defined in Section 10 – Stability and Reactivity Data. Store batteries in cool, dry, well-ventilated areas. Batteries should be stored under roof for protection against adverse weather conditions. Avoid damage to containers.

Other Precautions

GOOD PERSONAL HYGIENE AND WORK PRACTICES ARE MANDATORY. Refrain from eating, drinking or smoking in work areas.

Thoroughly wash hands, face, neck and arms, before eating, drinking and smoking. Work clothes and equipment should remain in designated lead contaminated areas, and never taken home or laundered with personal clothing. Wash soiled clothing, work clothes and equipment before reuse.

8. Exposure Controls and Personal Protection

Respiratory Protection (Specify Type)

None required under normal conditions. Acid/gas NIOSH approved respirator is required when the PEL is exceeded or employee experiences respiratory irritation.

Ventilation

Store and handle in dry ventilated area.

Local Exhaust

When PEL is exceeded.

Mechanical (General)

Not Applicable

Protective Gloves

Wear rubber or plastic acid resistant gloves.

Eye Protection

ANSI approved safety glasses with side shields/face shield recommended

Other Protective Clothing or Equipment

Safety shower and eyewash.



Material Safety Data Sheet

9. Physical and Chemical Properties

Boiling Point:	Not Applicable
Vapor Pressure:	Not Applicable
Specific Gravity:	1.250-1.320 pH <2
Melting Point:	>320°F (polypropylene)
Percent Volatile by Volume:	Not Applicable
Vapor Density:	Hydrogen: 0.069 (Air =1) Electrolyte: 3.4 @ STP (Air = 1)
Evaporation Rate:	Not applicable
Solubility in Water	100% soluble (electrolyte)
Reactivity in Water:	Electrolyte – Water Reactive (1)

Appearance and Odor:

Battery:	Co-polymer polypropylene, solid; may be contained within an outer casing of aluminum or steel. Case has metal terminals.
Lead:	Gray, metallic, solid; brown/grey oxide
Electrolyte:	Odorless, liquid absorbed in glass mat material. No apparent odor.

10. Stability and Reactivity

Stability:	Stable
Incompatibility (Materials to Avoid):	Sparks, open flames, keep battery away from strong oxidizers.
Conditions to Avoid:	Avoid overcharging and smoking, or sparks near battery surface. High temperatures-cases decompose at >320°F.
Hazardous Decomposition Products:	Combustion can produce carbon dioxide and carbon monoxide.
Hazardous Polymerization:	Hazardous Polymerization has not been reported.



Material Safety Data Sheet

11. Toxicological Information

GENERAL:

The primary routes of exposure to lead are ingestion or inhalation of dust and fumes.

ACUTE: INHALATION/INGESTION:

Exposure to lead and its compounds may cause headache, nausea, vomiting, abdominal spasms, fatigue, sleep disturbances, weight loss, anemia, and pain in the legs, arms and joints. Kidney damage, as well as anemia, can occur from acute exposure.

CHRONIC: INHALATION/INGESTION:

Prolonged exposure to lead and its compounds may produce many of the symptoms of short-term exposure and may also cause central nervous system damage, gastrointestinal disturbances, anemia, and wrist drop. Symptoms of central nervous system damage include fatigue, headaches, tremors, hypertension, hallucination, convulsions and delirium. Kidney dysfunction and possible injury has also been associated with chronic lead poisoning. Chronic over-exposure to lead has been implicated as a causative agent for the impairment of male and female reproductive capacity, but there is at present, no substantiation of the implication. Pregnant women should be protected from excessive exposure. Lead can cross the placental barrier and unborn children may suffer neurological damage or developmental problems due to excessive lead exposure in pregnant women.

12. Ecological Information

In most surface water and groundwater, lead forms compounds with anions such as hydroxides, carbonates, sulfates, and phosphates, and precipitates out of the water column. Lead may occur as sorbed ions or surface coatings on sediment mineral particles or may be carried in colloidal particles in surface water. Most lead is strongly retained in soil, resulting in little mobility. Lead may be immobilized by ion exchange with hydrous oxides or clays or by chelation with humic or fulvic acids in the soil. Lead (dissolved phase) is bioaccumulated by plants and animals, both aquatic and terrestrial.

13. Disposal Considerations

Lead-acid batteries are completely recyclable. Return whole scrap batteries to distributor, manufacturer or lead smelter for recycling. For neutralized spills, place residue in acid-resistant containers with sorbent material, sand or earth and dispose of in accordance with local, state and federal regulations for acid and lead compounds. Contact local and/or state environmental officials regarding disposal information.



Material Safety Data Sheet

14. Transport Information

The battery is a valve regulated lead acid (VRLA) batteries.

Our VRLA batteries have passed vibration, pressure differential and free flowing acid tests under CFR 49 173.159(d) and meet IATA Special Provisions A48 and A67. The batteries are securely packaged, protected from short circuits and labeled "Non-Spillable." Our VRLA batteries are exempt from DOT Hazardous Material Regulations and IATA 54th Dangerous packing instruction 965, section II Dangerous Goods Regulations.

Note: The shipper has the option of shipping the batteries Hazmat regulated under UN38.3. Additional labeling and paperwork would be required. See CFR 49 and IATA 54th Dangerous Goods Regulations for more information.

U.S. DOT PROPER SHIPPING NAME: Batteries, wet, non-spillable

U.S. DOT HAZARD CLASS: 8

U.S. DOT ID NUMBER: UN38.3

U.S. DOT PACKING GROUP: Section II

U.S. DOT LABEL: CORROSIVE

OR Excepted from the requirements because batteries have passed the Vibration and Pressure Differential performance tests, and ruptured case test for Nonspillable designation.

IMO PROPER SHIPPING NAME: Batteries, wet, non-spillable Ems # - F-A, S-B

IMO U.N. CLASS: 8

IMO U.N. NUMBER: UN 2800

IMO LABEL: CORROSIVE

IMO VESSEL STOWAGE: A

IATA PROPER SHIPPING NAME: Batteries, wet, non-spillable

IATA U.N. CLASS: 8

IATA U.N. NUMBER: UN 2800

IATA LABEL: CORROSIVE

ERG Code – 8L

Battery met special provision 238

Lead-Acid Rechargeable battery as per IMDG SP.238 And NON-DG-Shipment.

OR Excepted from the requirements because batteries have passed the vibration and pressure differential performance tests, and ruptured case test for nonspillable designation. And, when packaged for transport, the terminals are protected from short circuit.



Material Safety Data Sheet

15. Regulatory Information

U.S. HAZARDOUS UNDER HAZARD COMMUNICATION STANDARD:	LEAD - YES	
	ARSENIC - YES	
	SULFURIC ACID - YES	
INGREDIENTS LISTED ON TSCA INVENTORY:	YES	
CERCLA SECTION 304 HAZARDOUS SUBSTANCES:	LEAD - YES	RQ: N/A*
	ARSENIC - YES	RQ: 1 POUND
	SULFURIC ACID - YES	RQ: 1000 POUNDS
* RQ: REPORTING NOT REQUIRED WHEN DIAMETER OF THE PIECES OF SOLID METAL RELEASED IS EQUAL TO OR EXCEEDS 100 µm (micrometers).		
EPCRA SECTION 302 EXTREMELY HAZARDOUS SUBSTANCE:	SULFURIC ACID - YES	
EPCRA SECTION 313 TOXIC RELEASE INVENTORY:	LEAD - CAS NO: 7439-92-1	
	ARSENIC - CAS NO: 7440-38-2	
	SULFURIC ACID - CAS NO: 7664-93-9	

16. Other Information

THE INFORMATION ABOVE IS BELIEVED TO BE ACCURATE AND REPRESENTS THE BEST INFORMATION CURRENTLY AVAILABLE TO US. HOWEVER, WE MAKE NO WARRANTY OF MERCHANTABILITY OR ANY OTHER WARRANTY, EXPRESSED OR IMPLIED, WITH RESPECT TO SUCH INFORMATION, AND WE ASSUME NO LIABILITY RESULTING FROM ITS USE. USERS SHOULD MAKE THEIR OWN INVESTIGATIONS TO DETERMINE THE SUITABILITY OF THE INFORMATION FOR THEIR PARTICULAR PURPOSES. ALTHOUGH REASONABLE PRECAUTIONS HAVE BEEN TAKEN IN THE PREPARATION OF THE DATA CONTAINED HEREIN, IT IS OFFERED SOLELY FOR YOUR INFORMATION, CONSIDERATION AND INVESTIGATION.

THIS MATERIAL SAFETY DATA SHEET PROVIDES GUIDELINES FOR THE SAFE HANDLING AND USE OF THIS PRODUCT; IT DOES NOT AND CANNOT ADVISE ON ALL POSSIBLE SITUATIONS, THEREFORE, YOUR SPECIFIC USE OF THIS PRODUCT SHOULD BE EVALUATED TO DETERMINE IF ADDITIONAL PRECAUTIONS ARE REQUIRED.

The data/information contained herein has been reviewed and approved for general release on the basis that this document contains no export-controlled information.