

Item no.: 250848




## Material Safety Data Sheet

---

### 1. Product & Company Identification

<b>Product:</b>	Lithium Ion Rechargeable Battery (type 18650V1, ULF, EMMIHR18650PCHBG)
<b>Manufacturer:</b>	Conrad Electronic SE
<b>Nominal voltage:</b>	3,7 V
<b>Nominal capacity:</b>	1500 mAh
<b>Address:</b>	Klaus-Conrad-Str. 1, D-92240 Hirschau
<b>Telephone:</b>	+49 (0) 9604 / 40 - 8988
<b>Date of issue:</b>	28.05.2014

### 2. Hazards Identification

Protective Clothing	NFPA Rating (USA)	EC Classification	WHMIS (Canada)	Transportation	GHS Hazard Symbol
Not required with normal use		Not classified as Hazardous		See Section 14	 Signal Word: Warning

#### Preparation Hazards and Classification:

Not classified as dangerous or hazardous with normal use. The cell should not be opened or burned. Exposure to the ingredients contained within or their combustion products could be harmful.

European Communities (EC): This product is not classified as hazardous according to Regulation (EC) No. 1272/2008. This product contains dangerous ingredients however, there is no expected release during use of the product and there is a barrier preventing exposure of the user and the environment.

#### Appearance, Color and Odor:

Solid object with no odor.

#### Primary Route(s) of Exposure:

These chemicals are contained in a sealed enclosure. Risk of exposure occurs only if the cell is mechanically, thermally or electrically abused to the point of compromising the enclosure. If this occurs, exposure to the electrolyte solution contained within can occur by Inhalation, Ingestion, Eye contact and Skin contact.

Item no.: 250848

## Material Safety Data Sheet

---

### Potential Health Effects:

#### **ACUTE (short term): see Section 8 for exposure controls**

In the event that this cell has been ruptured, the electrolyte solution contained within the cell would be corrosive and can cause burns to skin and eyes.

#### **Inhalation:**

Inhalation of materials from a sealed cell is not an expected route of exposure. Vapors or mists from a ruptured cell may cause respiratory irritation.

#### **Ingestion:**

Swallowing of materials from a sealed cell is not an expected route of exposure. Swallowing the contents of an open cell can cause serious chemical burns of mouth, esophagus, and gastrointestinal tract.

#### **Skin:**

Contact between the cell and skin will not cause any harm. Skin contact with contents of an open cell can cause severe irritation or burns to the skin.

#### **Eye:**

Contact between the cell and the eye will not cause any harm. Eye contact with contents of an open cell can cause severe irritation or burns to the eye.

#### **CHRONIC (long term): see Section 11 for additional toxicological data**

Not applicable

#### **Medical Conditions Aggravated by Exposure:**

Not available

#### **Interactions With Other Chemicals:**

Immersion in high conductivity liquids may cause corrosion and breaching of the cell enclosure.

#### **Potential Environmental Effects:**

Not available

### 3. Composition/Information on Ingredients

As a solid, manufactured article, exposure to hazardous ingredients is not expected with normal use.

USA: This cell is an article pursuant to 29 CFR 1910.1200 and, as such, is not subject to the OSHA Hazard Communication Standard requirement. The information contained in this Safety Data Sheet contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product.

Canada: This is not a controlled product under WHMIS. This product meets the definition of a "manufactured article" and is not subject to the regulations of the Hazardous Products Act.

## Material Safety Data Sheet

---

### 4. First Aid Measures

**Inhalation:**

If contents of an opened cell are inhaled, remove source of contamination or move victim to fresh air. Obtain medical advice.

**Eye Contact:**

Contact with the contents of an opened cell can cause burns. If eye contact with contents of an open cell occurs, immediately flush the contaminated eye(s) with lukewarm, gently flowing water for at least 30 minutes while holding the eyelids open. Neutral saline solution may be used as soon as it is available. If necessary, continue flushing during transport to emergency care facility. Take care not to rinse contaminated water into the unaffected eye or onto face. Quickly transport victim to an emergency care facility.

**Skin Contact:**

Contact with the contents of an opened cell can cause burns. If skin contact with contents of an open cell occurs, as quickly as possible remove contaminated clothing, shoes and leather goods. Immediately flush with lukewarm, gently flowing water for at least 30 minutes. If irritation or pain persists, seek medical attention. Completely decontaminate clothing, shoes and leather goods before reuse or discard.

**Ingestion:**

Contact with the contents of an opened cell can cause burns. If ingestion of contents of an open cell occurs, NEVER give anything by mouth if victim is rapidly losing consciousness, or is unconscious or convulsing. Have victim rinse mouth thoroughly with water. DO NOT INDUCE VOMITING. If vomiting occurs naturally, have victim lean forward to reduce risk of aspiration. Have victim rinse mouth with water again. Quickly transport victim to an emergency care facility.

### 5. Fire Fighting Measures

**Flammable Properties:**

Lithium ion batteries contain flammable liquid electrolyte that may vent, ignite and produce sparks when subjected to high temperatures (> 150 °C (302 °F)), when damaged or abused (e.g., mechanical damage or electrical overcharge). Burning cells can ignite other batteries in close proximity.

**Suitable extinguishing Media:**

Small Fires - Dry chemical, CO<sub>2</sub>, water spray or regular foam.

Large Fires - Water spray, fog or regular foam. Move containers from fire area if you can do it without risk.

**Unsuitable extinguishing Media:**

Not Applicable

**Explosion Data:**

Sensitivity to Mechanical Impact: Extreme mechanical abuse will result in rupture of the individual battery cells.

Sensitivity to Static Discharge: Electrostatic discharges imposed directly on the spilled electrolyte may start combustion.

**Specific Hazards arising from the Chemical:**

The interaction of water or water vapor and exposed lithium hexafluorophosphate (Li PF<sub>6</sub>) may result in the generation of hydrogen and hydrogen fluoride (HF) gas.

Contact with battery electrolyte may be irritating to skin, eyes and mucous membranes. Fire will produce irritating, corrosive and/or toxic gases. Fumes may cause dizziness or suffocation.

Protective Equipment and precautions for firefighters:

Wear positive pressure self-contained breathing apparatus (SCBA). Structural firefighters' protective clothing will only provide limited protection. Fight fire from a safe distance.

**NFPA:** Health: 0 Flammability: 1 Instability: 0

## Material Safety Data Sheet

---

### 6. Accidental Release Measures

**Personal Precautions:**

As an immediate precautionary measure, isolate spill or leak area for at least 25 meters (75 feet) in all directions. Keep unauthorized personnel away. Stay upwind. Keep out of low areas. Ventilate closed areas before entering.

Wear adequate personal protective equipment as indicated in Section 8.

**Environmental Precautions:**

Prevent material from contaminating soil and from entering sewers or waterways.

**Methods for Containment:**

Stop the leak if safe to do so. Contain the spilled liquid with dry sand or earth. Clean up spills immediately.

**Methods for Clean-up:**

Absorb spilled material with an inert absorbent (dry sand or earth). Scoop contaminated absorbent into an acceptable waste container. Collect all contaminated absorbent and dispose of according to directions in Section 13. Scrub the area with detergent and water; collect all contaminated wash water for proper disposal.

### 7. Handling and Storage

**Handling/Transportation:**

Do not open, disassemble, crush or burn cell. Do not expose cell to temperatures outside the range of -40°C to 80°C.

**Storage:**

Store cell in a dry location. To minimize any adverse effects on battery performance it is recommended that the cells be kept at room temperature (25°C +/- 5°C). Elevated temperatures can result in shortened cell life. Keep out of reach of children.

### 8. Exposure Controls/Personal Protection

**Exposure Limit Values:**

Airborne exposures to hazardous substances are not expected when product is used for its intended purpose.

**Engineering Controls:**

Use local exhaust ventilation or other engineering controls to control sources of dust, mist, fume and vapor.

**Personal Protection:**

**Respiratory Protection:**

Not necessary under normal conditions.

**Skin Protection:**

Not necessary under normal conditions. Wear neoprene or natural rubber gloves if handling an open or leaking cell.

**Eye Protection:**

Not necessary under normal conditions. Wear safety glasses if handling an open or leaking cell.

**Other Protective Equipment:**

Not necessary under normal conditions. Have a safety shower and eye-wash fountain readily available in the immediate work area.

**Hygiene Measures:**

Do not eat, drink or smoke in work areas. Maintain good housekeeping.

## Material Safety Data Sheet

---

### 9. Physical and Chemical Properties

<b>Physical State:</b>	Solid	<b>Vapor Pressure (mm Hg @ 20°C):</b>	Not applicable
<b>Appearance:</b>	Cell	<b>Vapor Density:</b>	Not applicable
<b>pH:</b>	Not applicable	<b>Solubility in Water:</b>	Insoluble
<b>Relative Density:</b>	Not available	<b>Water / Oil distribution coefficient:</b>	Not applicable
<b>Boiling Point:</b>	Not applicable	<b>Odor Type:</b>	Odorless
<b>Melting Point:</b>	Not applicable	<b>Odor Threshold:</b>	Not applicable
<b>Viscosity:</b>	Not applicable	<b>Evaporation Rate:</b>	Not applicable
<b>Oxidizing Properties:</b>	Not applicable	<b>Auto Ignition Temperature (°C):</b>	Not applicable
<b>Flash Point and Method (°C):</b>	Not applicable	<b>Flammability Limits (%):</b>	Not applicable

### 10. Stability and Reactivity

**Stability:**

Stable

**Conditions to Avoid:**

Avoid exposing the cell to fire or temperatures above 80°C. Do not disassemble, crush, short or install with incorrect polarity. Avoid mechanical or electrical abuse.

**Incompatible Materials:**

Do not immerse in seawater or other high conductivity liquids.

**Hazardous Decomposition Products:**

This material may release toxic fumes if burned or exposed to fire. Breaching of the cell enclosure may lead to generation of hazardous fumes which may include extremely hazardous HF (hydrofluoric acid).

**Possibility of Hazardous Reactions:**

Not available

## Material Safety Data Sheet

---

### 11. Toxicological Information

#### Acute Toxicity Data

Acute oral, dermal and inhalation toxicity data are not available for this article.

#### Other Toxicity Data

##### Irritation:

Risk of irritation occurs only if the cell is mechanically, thermally or electrically abused to the point of compromising the enclosure. If this occurs, irritation to the skin, eyes and respiratory tract may occur.

##### Corrosivity:

Not applicable

##### Sensitization:

Not available

##### Neurological Effects:

Not applicable

##### Genetic Effects:

Not applicable

##### Reproductive Effects:

Not applicable

##### Developmental Effects:

Not applicable

##### Target Organ Effects:

Not applicable

##### Carcinogenicity:

Normal safe handling of this product will not result in exposure to substances that are considered human carcinogens by IARC (International Agency for Research on Cancer), ACGIH (American Conference of Governmental Industrial Hygienists, OSHA or NTP (National Toxicology Program).

## Material Safety Data Sheet

---

### 12. Ecological Informations

**Ecotoxicity:**

Not available

**Mobility:**

Not available

**Persistence and degradability:**

Not readily biodegradable

**Bioaccumulative potential:**

Not available

**Other adverse effects:**

Solid cells released into the natural environment will slowly degrade and may release harmful or toxic substances. Cells are not intended to be released into water or on land but should be disposed or recycled according to local regulations.

### 13. Disposal Considerations

**Waste Disposal Method:**

Cell recycling is encouraged. Do NOT dump into any sewers, on the ground or into any body of water. Store material for disposal as indicated in Section 7 Handling and Storage.

**USA:** Dispose of in accordance with local, state and federal laws and regulations.

**Canada:** Dispose of in accordance with local, provincial and federal laws and regulations.

**EC:** Waste must be disposed of in accordance with relevant EC Directives and national, regional and local environmental control regulations. For disposal within the EC, the appropriate code according to the European Waste Catalogue (EWC) should be used.

### 14. Transport Information

Our lithium-ion cells and batteries are designed to comply with all applicable shipping regulations as prescribed by industry and legal standards which includes compliance with the UN Recommendations on the Transport of Dangerous Goods; IATA Dangerous Goods Regulations and applicable U.S. DOT regulations for the safe transport of lithium-ion batteries and the International Maritime Dangerous Goods Code. Each battery has passed the UN Manual of Tests and Criteria Part III Subsection 38.3, which is required by all of the directives listed above.

In the US, shipments of lithium ion cells and batteries are classified as Class 9, UN3480, Packing Group II, by the U.S. Hazardous Materials Regulations (HMR). Packaging, markings and documentation requirements are defined in Title 49 of the Code of Federal Regulations (CFR), Section 173.185. of the U.S. HMR. Excepted cells and batteries are allowed to be transported within the US without Class 9 packaging and markings, but must conform to other requirements as stipulated in Special Provisions 188 and 189 in the 49 CFR Section 173.185 of the U.S. HMR.

International shipments of lithium ion cells and batteries are generally classified as Class 9, UN3480, Packing Group II, by the International Civil Aviation Organization (ICAO) and the International Maritime Dangerous Goods (IMDG) Code. Packaging, markings and documentation requirements are defined in the International Air Transport Association (IATA) Dangerous Goods Regulations (DGR) Packing Instructions 965 and Packing Instruction P903 of the IMDG Code. Excepted cells and batteries are allowed to be transported internationally without Class 9 packaging and in some circumstances markings, but must conform to other requirements as stipulated in Packing Instructions 965 of the IATA DGR and Special Provision 188 under the IMDG Code.

Item no.: 250848

## Material Safety Data Sheet

### 15. Regulatory Information

#### USA

**TSCA Status:** All ingredients in the product are listed on the TSCA inventory.

**SARA Title III:** None

Sec. 302/304: None

Sec. 311/312: None

Sec. 313: None

CERCLA RQ

**California Prop 65 :** This product does not contain chemicals known to the State of California to cause cancer or reproductive toxicity.

#### Canada

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

**WHMIS Classification:** Not Controlled

**New Substance Notification Regulations:** Lithium hexafluorophosphate is listed on the NDSL. All other ingredients in the product are listed, as required, on Canada's Domestic Substances List (DSL).

**NPRI Substances:** This product does not contain any NPRI chemicals.

#### EC Classification for the Substance/Preparation:

This product is not classified as hazardous according to Regulation (EC) No. 1272/2008. Keep out of the reach of children.

#### EINECS Status:

Cell component	Chemical Name	CAS No.	EINECS	Concentration range in electrolyte (w/w %)	Mass range in cell (g/g %)
Electrolyte salt	Lithium hexafluorophosphate	21324-40-3	244-334-7	10 - 20	1 - 5
Electrolyte solvents	Includes one or more of the following:			80 - 90	10 - 20
	Ethylene Carbonate,	96-49-1	202-510-0		
	Propylene Carbonate,	108-32-7	203-572-1		
	Diethyl Carbonate,	105-58-8	203-311-1		
	Dimethyl Carbonate	616-38-6	210-478-4		
	Ethyl Methyl Carbonate	623-53-0	Not Listed		

### 16. Other Information

#### Manufacturer Disclaimer:

The information and recommendations set forth are made in good faith and believed to be accurate at the date of preparation.