

**HDC insert  
HDC HE 24 MP 25-48****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The PUSH IN connection is a direct-insert method of connection. The prepared wire can be inserted directly into the wire connection level without the need for any additional tools.

PUSH IN technology

**General ordering data**

|            |                                                                  |
|------------|------------------------------------------------------------------|
| Type       | HDC HE 24 MP 25-48                                               |
| Order No.  | <a href="#">1875890000</a>                                       |
| Version    | HDC insert, Pin, 500 V, 16 A, No. of poles: 24, PUSH IN, Size: 8 |
| GTIN (EAN) | 4032248466153                                                    |
| Qty.       | 1 pc(s).                                                         |

## HDC insert HDC HE 24 MP 25-48

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 34 mm   | Width (inches)  | 1.339 inch |
| Height     | 34.3 mm | Height (inches) | 1.35 inch  |
| Depth      | 111 mm  | Depth (inches)  | 4.37 inch  |
| Net weight | 104.9 g |                 |            |

### Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Dimensions

|                |         |                   |        |
|----------------|---------|-------------------|--------|
| Height of plug | 34.3 mm | Total length base | 111 mm |
|----------------|---------|-------------------|--------|

### General data

|                                      |                                                             |                              |                   |
|--------------------------------------|-------------------------------------------------------------|------------------------------|-------------------|
| Insulating material                  | PC glass-fibre reinforced (UL-listed and railway-certified) | Insulating material group    | IIIa              |
| Insulation strength                  | $10^{10} \Omega$                                            | Material                     | Copper alloy      |
| No. of poles                         | 24                                                          | Plugging cycles, silver      | $\geq 500$        |
| Pollution severity                   | 3                                                           | Rated current (DIN EN 61984) | 16 A              |
| Rated impulse voltage (DIN EN 61984) | 6 kV                                                        | Rated voltage (DIN EN 61984) | 500 V             |
| Rated voltage according to UL/CSA    | 600 V AC/DC                                                 | Series                       | HE                |
| Size                                 | 8                                                           | Surface finish               | Silver passivated |
| Type                                 | Pin                                                         | UL 94 flammability rating    | V-0               |
| Volume resistance                    | $\leq 2\text{m}\Omega$                                      |                              |                   |

### Connection data PE

|                                                                                         |                     |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------|---------------------|
| Blade size, crosshead                                                                   | size PH 1           | Blade size, slotted (PE connection)                                                     | SD 0.8 x 4.0        |
| Connection type PE                                                                      | Screw connection    | Fixing screw                                                                            | M 4                 |
| Rated cross-section                                                                     | 4 mm <sup>2</sup>   | Stripping length PE connection                                                          | 10 mm               |
| Tightening torque, max. PE connection                                                   | 1.5 Nm              | Tightening torque, min. PE connection                                                   | 1.2 Nm              |
| Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire cross section, AWG (PE), max.                                                      | AWG 12              | Wire cross section, AWG (PE), min.                                                      | AWG 20              |
| Wire cross-section, solid, max.                                                         | 1.5 mm <sup>2</sup> | Wire cross-section, solid, min.                                                         | 0.5 mm <sup>2</sup> |

## HDC insert HDC HE 24 MP 25-48

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Version

|                                                                                         |                        |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------------------------|---------------------|
| Blade size, slotted (screw connection)                                                  | SD 0.5 x 3.0           | Material                                                                                | Copper alloy        |
| Size                                                                                    | 8                      | Stripping length, rated connection                                                      | 10 mm               |
| Surface finish                                                                          | Silver passivated      | Type of connection                                                                      | PUSH IN             |
| Volume resistance                                                                       | $\leq 2\text{m}\Omega$ | Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>    | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup>    | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>    | Wire cross-section, solid, max.                                                         | 1.5 mm <sup>2</sup> |
| Wire cross-section, solid, min.                                                         | 0.5 mm <sup>2</sup>    |                                                                                         |                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001121    | ETIM 4.0   | EC000438    |
| ETIM 5.0   | EC000438    | ETIM 6.0   | EC000438    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-34-19 |
| eClass 6.2 | 27-26-12-04 | eClass 7.1 | 27-44-02-05 |
| eClass 8.1 | 27-44-02-05 | eClass 9.0 | 27-44-02-05 |
| eClass 9.1 | 27-44-02-05 |            |             |

### Approvals

Approvals



ROHS

Conform


### Downloads

|                    |                                                                         |
|--------------------|-------------------------------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">FL FIELDWIRING EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>                                            |
| Engineering Data   | <a href="#">STEP</a>                                                    |

## HDC insert HDC HE 24 MP 25-48

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Tightening torques and screwing tools

| Screw size         | Connector type                          | Dia. tightening torque in Nm                                                      | Recommended blade inserts and AF size for hexagon socket |
|--------------------|-----------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------|
| <b>M 2.5</b>       | <b>Signal contacts</b>                  |                                                                                   |                                                          |
|                    | S 6/6                                   | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | S 6/12                                  | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
| <b>M 2.9 x 0.5</b> | <b>Fastening screws</b>                 |                                                                                   |                                                          |
|                    | HQ 4/2                                  | 0.8 (plastic) / 1.1 (metal)                                                       | SD 0.6 x 3.5 mm or PH0                                   |
|                    | HQ 8                                    | 0.8 (plastic) / 1.1 (metal)                                                       | SD 0.6 x 3.5 mm or PH0                                   |
|                    | HQ 17                                   | 0.8 (plastic) / 1.1 (metal)                                                       | SD 0.6 x 3.5 mm or PH0                                   |
| <b>M 3</b>         | <b>Contact screws</b>                   |                                                                                   |                                                          |
|                    | HA 3                                    | 0.5 - 0.55                                                                        | SD 0.5 x 3.0 mm                                          |
|                    | HA 4                                    | 0.5 - 0.55                                                                        | SD 0.5 x 3.0 mm                                          |
|                    | HA 10 bis HA 48                         | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PH0                                   |
|                    | HE                                      | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | HVE                                     | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | <b>Signal contacts:</b>                 |                                                                                   |                                                          |
|                    | S 4/2                                   | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | S 4/8                                   | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | <b>PE connection via female contact</b> |                                                                                   |                                                          |
|                    | S 4                                     | 0.5 - 0.8                                                                         | SD 0.6 x 3.5 mm                                          |
|                    | ConCept modular frame, metal            | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm                                          |
|                    | <b>PE terminal</b>                      |                                                                                   |                                                          |
|                    | HQ 5                                    | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 or 0.8 x 4 mm                               |
|                    | HQ 7                                    | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 or 0.8 x 4 mm                               |
|                    | <b>Fastening screws</b>                 | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | <b>Guide pin</b>                        | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | <b>Guide bush</b>                       | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
|                    | <b>Coding pins</b>                      | 0.5 - 0.55                                                                        | SD 0.6 x 3.5 mm or PZ0                                   |
| <b>M 4</b>         | <b>Contact screws</b>                   |                                                                                   |                                                          |
|                    | HSB                                     | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PZ1                        |
|                    | <b>PE connection via male contact</b>   |                                                                                   |                                                          |
|                    | S 4                                     | 0.5 - 0.8                                                                         | SD 0.6 x 3.5 mm                                          |
|                    | ConCept modular frame, metal            | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 mm                                          |
|                    | <b>PE terminal</b>                      |                                                                                   |                                                          |
|                    | HA                                      | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PH1                        |
|                    | HE                                      | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PH1                        |
|                    | HEE                                     | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PH1                        |
|                    | HVE                                     | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PH1                        |
|                    | HD                                      | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PZ1                        |
|                    | HDD                                     | 1.2 - 1.5                                                                         | SD 0.6 x 3.5 or 0.8 x 4 mm or PZ1                        |
|                    | S 6/6 (for signal contacts)             | 1.2 - 1.5                                                                         | 0.8 x 4 mm or PZ1                                        |
|                    | ConCept modular frame, plastic          | 1.2 - 1.5                                                                         | 0.8 x 4 mm or PZ1                                        |
| <b>M 5</b>         | <b>PE terminal</b>                      |                                                                                   |                                                          |
|                    | HSB                                     | 2 - 2.5                                                                           | SD 1 x 5.5 mm or PZ2                                     |
|                    | S 4/0 (Screw connection)                | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
|                    | S 4/0 (Axial screw connection)          | 2 - 2.5                                                                           | SD 0.8 x 4 mm or PZ 2                                    |
|                    | S 4/2                                   | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
|                    | S 4/8                                   | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
|                    | S 6/12                                  | 2 - 2.5                                                                           | SD 0.8 x 4 mm or PZ 2                                    |
|                    | S 6/36                                  | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
|                    | S 8/24                                  | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
|                    | S 12/2                                  | 2 - 2.5                                                                           | SD 1.2 x 6.5 mm or PH2                                   |
| <b>M 6</b>         | <b>Power contacts</b>                   |                                                                                   |                                                          |
|                    | S 4/0 (Screw connection)                | 1.2 (1.5 mm <sup>2</sup> ) / 2 (2.5 mm <sup>2</sup> ) / 3 (4-16 mm <sup>2</sup> ) | SD 0.8 x 4 mm                                            |
|                    | S 4/2                                   | 1.2 (1.5 mm <sup>2</sup> ) / 2 (2.5 mm <sup>2</sup> ) / 3 (4-16 mm <sup>2</sup> ) | SD 0.8 x 4 mm                                            |
|                    | S 4/8                                   | 1.2 (1.5 mm <sup>2</sup> ) / 2 (2.5 mm <sup>2</sup> ) / 3 (4-16 mm <sup>2</sup> ) | SD 0.8 x 4 mm                                            |
| <b>M 7 x 0.75</b>  | <b>Power contacts</b>                   |                                                                                   |                                                          |
|                    | S 4                                     | 1.1 - 1.7                                                                         | SW 2                                                     |
|                    | S 6/6 (+ PE)                            | 6 - 8                                                                             | SW 4                                                     |
| <b>M 8 x 0.75</b>  | <b>Power contacts</b>                   |                                                                                   |                                                          |
|                    | S 6/12                                  | 1.1 - 1.7                                                                         | SW 2                                                     |
|                    | S 8/0 (+ PE)                            | 6 (10-16 mm <sup>2</sup> ) - 7 (25 mm <sup>2</sup> )                              | SW 4                                                     |
| <b>M10 x 1</b>     | <b>Power contacts</b>                   |                                                                                   |                                                          |
|                    | S 4/0 (Axial connection)                | 2 - 3                                                                             | SW 3                                                     |

Increasing the tightening torque does not improve the contact resistance. The stated torque settings offer optimal mechanical, thermal and electrical conditions. Exceeding the recommended values may even damage the conductor and terminal.