



DATA SHEET

Туре	: Rechargeable Nickel Metal
Type	Hydride Cylindrical Cell
Nominal Dimension	: Φ = 10.4mm
(with Sleeve)	H = 29.3mm
Applications	: Recommended discharge current
, approations	40 to 1200mA
Nominal Voltage	: 1.2V
Capacity	: Rated: 400mAh
. ,	Typical: 420mAh
	When discharged at 80mA to
	1.0V at 20℃
Charging Condition	: 40mA for 16 hrs at 20°C
Charging Retention	: 80% of rated capacity after cell storage at 20
	°C for 12 months
	When discharged at 80mA to 1.0V at 20°C
Fast Charge	: 200mA to 400mA (0.5 to 1C)
	charge termination control recommended
	control parameters:
	$-\Delta V$: $0-5mV$
	DT/dt : 0.8° C/min (0.5 to 0.9C)
	0.8 - 1°C/min (1C)
	TCO : 45 - 50°C
	Timer : 105% nominal input
	(for ref. only)
Service Life	: > 500 cycles (IEC standard)
Continuous	: 40mA maximum current for 1 year.
Overcharge	No conspicuous deformation and/or
	leakage
Weight	: 8.0g
Internal Resistance	: Average 65mΩ upon fully charged
	(Max. 80mΩ) at 1000Hz
Max. Charging Voltage	: 1.5V at 40mA charging
Ambient Temperature	: Standard Charge : 0 to 45°C
Range	Fast Charging : 10 to 45℃
	Discharge : -20 to 50°C
	Storage : -20 to 35℃


Model No.: GP40AAAM




Low Rate Discharge



Fast Charge (Charge Control Required)



High Rate Discharge



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com

TRS0219 rev.07