

ICP621333PA

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
Safety Circuit, Wire

Specifications

Renata Type	ICP621333
IEC Designation	ICP071335
Part Number	100693
Contact:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	240 mAh
Minimum Capacity	230 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 410 mΩ / 50% SOC

Thickness (t)	Max 6.7 mm
Length (l)	Max 13.0 mm
Width (w)	Max 35.0 mm
Weight	~ 5.5 g


Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 120 mA
Max. Charging Current	1.0 C CC – 240 mA
Temperature at Charging	0 °C 45 °C

Discharge Characteristic	
Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 480 mA (for non continues discharge) 1.0 C – 240 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.