

## ICP521630PM

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V  
Safety Circuit

### Specifications

Renata Type	ICP521630
IEC Designation	ICP061732
Part Number	100691
Contact Method:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	250 mAh
Minimum Capacity	240 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 260 mΩ / 50% SOC

Thickness ( t )	Max 5.7 mm
Length ( l )	Max 31.5 mm
Width ( w )	Max 17.0 mm
Weight	~ 5.4 g


<b>Charging Characteristic</b>	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 125 mA
Max. Charging Current	1.0 C CC – 250 mA
Temperature at Charging	0 °C .... 45 °C

<b>Discharge Characteristic</b>	
Cut off Voltage	3.0 V
Max discharge Current	2.0 C – 500 mA ( for non continues discharge ) 1.0 C – 250 mA ( for continues discharge )
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles ( 0.5 C charge, 0.5 C discharge )
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C ( 0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

### Dimensions



*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.*

Rev. Li Ion ICP521630 – 11.09