

K MOPL K3 NT FE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The enclosures are ideal for turnkey customised solutions for standard industrial applications and for explosive-risk applications.

Improved products that meet all application requirements: this was Weidmüller's aim during the update of the Klippon® K housing series. Weidmüller delivers many types of aluminium enclosures; they are designed to fit precisely with a wide range of customer requirements and applications.

Our comprehensive product line provides the following advantages:

- Available in two different surfaces: natural and powder-coated (RAL 7001)
- Available normally with silicone or chloroprene gasket seal
- A uniform Torx-slotted screw head is used for over 19 different housing sizes.
- Mounting holes not within the sealed area
- High degree of protection: IP66, IP67 and IP68
- Impact resistance of up to 10 Joules
- The housings are certified by ATEX, GOST, GOST Ex, cULus, Russian Maritime Register, German Lloyd, as well as the empty housing standard.
- Alloy is resistant to salt water

- Standardised distributor housings with threaded holes and a variety of terminal configurations

General ordering data

Type	MOPL K3 NT FE
Order No.	1899630000
Version	Mounting plate, Mounting Plate, Sheet steel, galvanised, 156 mm
GTIN (EAN)	4032248519613
Qty.	1 pc(s).

**K
MOPL K3 NT FE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Width	156 mm	Mounting dimension - width	147 mm
Net weight	76 g		

General information

Material thickness	2 mm	Material	Sheet steel, galvanised
--------------------	------	----------	-------------------------

General information on accessories

Material	Sheet steel, galvanised	Material thickness	2 mm
Mounting dimension - width	147 mm		

Classifications

ETIM 3.0	EC000318	UNSPSC	31-16-23-03
eClass 5.1	27-18-92-07	eClass 6.2	27-18-92-34
eClass 7.1	27-18-92-34		

Approvals

Approvals	
ROHS	Conform