

LIFE COLOURS

00336-0003

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LIFE COLOURS

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Paint

1.3. Details of the supplier of the safety data sheet

Elita Modelle Klaus Kutschka

Am Galgenbuck 6

D-90613 Großhabersdorf

Telephone: +49 (0) 9105-990018

Telefax: +49 (0) 9105-990082

e-mail: info@elita.de

Contact person: Klaus Kutschka Telephone: +49 (0) 9105-990018

http://www.elita.de

Responsible for the safety data sheet: sds@gbk-ingelheim.de

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Indications of danger : Irritant

R-phrases:

Flammable.

Irritating to eyes.

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

GHS classification

Hazard categories:

Flammable liquid: Flam. Liq. 3

Serious eye damage/eye irritation: Eye Dam. 1

Hazardous to the aquatic environment: Aquatic Chronic 3

Hazard Statements:

Flammable liquid and vapour.

Causes serious eye damage.

Harmful to aquatic life with long lasting effects.

2.2. Label elements

Pictograms:

GHS02-GHS05



Signal word:

Danger

Hazardous components which must be listed on the label

Butyl glycollate

Hazard statements

H226 Flammable liquid and vapour.

H318 Causes serious eye damage.

H412 Harmful to aquatic life with long lasting effects.

Precautionary statements

P102 Keep out of reach of children.

P101 If medical advice is needed, have product container or label at hand.

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P501 Dispose of contents/container to in accordance with local and national regulations.

LIFE COLOURS

00336-0003

2.3. Other hazards

Vapours may form explosive mixture with air.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Chemical characterization

Mixture of organic solvents

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification	
Index No	GHS classification	
REACH No		
204-626-7	4-Hydroxy-4-methylpentan-2-one	10 - 25 %
123-42-2	Xi - Irritant R36	
603-016-00-1	Eye Irrit. 2; H319	
265-199-0	Solvent naphta (petroleum)	5 - 10 %
64742-95-6	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-37-51-53-65-66-67 Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H335 H336 H304 H411	
01-2119455851-35		
252-104-2	(2-methoxymethylethoxy)propanol	5 - 10 %
34590-94-8		
230-991-7	Butyl glycollate	5 - 10 %
7397-62-8	Xi - Irritant R41 Eye Dam. 1; H318	
202-436-9	1,2,4-Trimethylbenzene	2,5 - 5 %
95-63-6	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-20-36/37/38-51-53	
601-043-00-3	Flam. Liq. 3, Acute Tox. 4, Eye Irrit. 2, STOT SE 3, Skin Irrit. 2, Aquatic Chronic 2; H226 H332 H319 H335 H315 H411	
203-604-4	Trimethylbenzenes, all isomers or mixtures	< 1 %
108-67-8	Xi - Irritant, N - Dangerous for the environment R10-37-51-53	
601-025-00-5	Flam. Liq. 3, STOT SE 3, Aquatic Chronic 2; H226 H335 H411	
202-704-5	Cumene	< 1 %
98-82-8	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-65-37-51-53	
601-024-00-X	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2; H226 H304 H335 H411	

Full text of R and H phrases: see Section 16.

Further Information

According to note P to the regulation (EC) no. 1272/2008, "Solvent naphta (petroleum)" is not to be classified as "carcinogenic" or "mutagen" ingredient because a benzene content (EINECS No. 200-753-7) is below 0.1 % by weight.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated soaked clothing immediately.
If you feel unwell, seek medical advice.
Adhere to personal protective measures when giving first aid.

After inhalation

Move to fresh air in case of accidental inhalation of vapours.
In the event of symptoms refer for medical treatment.

After contact with skin

Wash off immediately with plenty of water and soap for at least 15 minutes.
Consult a doctor if skin irritation persists.

After contact with eyes

Remove contact lens.
Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

LIFE COLOURS

00336-0003

Seek medical treatment by eye specialist.

After ingestion

Do not induce vomiting.
Rinse out mouth and give plenty of water to drink.
Never give anything by mouth to an unconscious person.
Summon a doctor immediately.
Induce vomiting only upon the advice of a physician.

4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Foam, carbon dioxide (CO₂), dry chemical, water-spray.

Extinguishing media which must not be used for safety reasons

Full water jet.

5.2. Special hazards arising from the substance or mixture

Fire may produce:
Irritant/corrosive, flammable as well as toxic distillation gases (carbonization gases).

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective suit.

Additional information

Cool containers at risk with water spray jet.
The vapour/air mixture is explosive, even in empty, uncleaned receptacles.
Do not release chemically contaminated water into drains, soil or surface waters. Sufficient measures must be taken to retain water used for extinguishing.
Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

In case of vapour formation use respirator.
Use only explosion-proof equipment.
Ensure adequate ventilation.
Remove persons to safety.
Use personal protective clothing.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.
Do not discharge into the subsoil/soil.

6.3. Methods and material for containment and cleaning up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder).
Shovel into suitable container for disposal.
Clean contaminated surface thoroughly.

6.4. Reference to other sections

Observe protective instructions (see Sections 7 and 8).
Information for disposal look up chapter 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Keep container tightly closed.
Vapours are heavier than air and spread along ground.
Avoid contact with the skin and the eyes.
Do not breathe vapours.

LIFE COLOURS

00336-0003

Advice on protection against fire and explosion

Do not smoke - volatile.
Keep away from heat and sources of ignition.
Take precautionary measures against static discharges.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a dry, cool and well-ventilated place.
Pay attention to anti-explosion rules.
Recommended storage temperature: 5 - 35°C

Advice on storage compatibility

Incompatible with:
Acids and bases.
Oxidizing agents

Further information on storage conditions

Keep away from food, drink and animal feeding stuffs.

7.3. Specific end use(s)

Paint

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Chemical name	ml/m ³	mg/m ³	F/ml	Category	Origin
34590-94-8	(2-methoxymethylethoxy) propanol	50	308		TWA (8 h)	WEL
		-	-		STEL (15 min)	WEL
123-42-2	4-Hydroxy-4-methyl-pentan-2-one	50	241		TWA (8 h)	WEL
		75	362		STEL (15 min)	WEL
98-82-8	Cumene	25	125		TWA (8 h)	WEL
		50	250		STEL (15 min)	WEL
108-67-8	Trimethylbenzenes	25	125		TWA (8 h)	WEL
		-	-		STEL (15 min)	WEL
95-63-6	Trimethylbenzenes	25	125		TWA (8 h)	WEL
		-	-		STEL (15 min)	WEL

8.2. Exposure controls

Occupational exposure controls

Ensure adequate ventilation, especially in confined areas.

Protective and hygiene measures

Do not inhale vapours.
Wash hands before breaks and immediately after handling the product.
When using, do not eat, drink or smoke.
Take off immediately all contaminated clothing.
Avoid contact with skin, eyes and clothing.

Respiratory protection

In case of insufficient ventilation wear suitable respiratory equipment (gas filter type A).

Hand protection

Protective gloves resistant to chemicals made off butyl, minimum coat thickness 0,7 mm, permeation resistance (wear duration) approx. 480 minutes, i.e. protective glove <Butoject 898> made by www.kcl.de.
This recommendation refers exclusively to the chemical compatibility and the lab test conforming to EN 374 carried out under lab conditions.
Requirements can vary as a function of the use. Therefore it is necessary to adhere additionally to the recommendations given by the manufacturer of protective gloves.

Eye protection

Tightly fitting goggles.

LIFE COLOURS

00336-0003

Eye wash bottle with pure water.

Skin protection

Light protective clothing

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state: Viscous liquid
Colour: Various
Odour: characteristic

Test method

Changes in the physical state

Boiling point: > 160 °C
Flash point: > 40 °C

Explosive properties

The product is considered non-explosive; nevertheless explosive vapour/air mixture can be generated.

Lower explosion limits: 0,9 vol. %
Upper explosion limits: 6,9 vol. %
Ignition temperature: n.d.
Vapour pressure: n.d.
(at 20 °C)
Density (at 15 °C): 1,12 g/cm³
Water solubility: n.d.
(at 20 °C)

SECTION 10: Stability and reactivity

10.1. Reactivity

No decomposition if stored and applied as directed.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Reactions with acids, alkalies and oxidizing agents.

10.4. Conditions to avoid

To avoid thermal decomposition, do not overheat.
Vapour/air mixtures are explosive at intensive warming.
Heating can release vapours which can be ignited.

10.5. Incompatible materials

Acids and bases.
Oxidizing agents

10.6. Hazardous decomposition products

No hazardous decomposition products known.
Fire may produce:
Irritant/corrosive, flammable as well as toxic distillation gases (carbonization gases).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

No toxicological data available.

Irritation and corrosivity

Skin irritation: Not classified.
Eye irritation: Causes serious eye damage.

Sensitising effects

Not classified.

LIFE COLOURS

00336-0003

Severe effects after repeated or prolonged exposure

STOT - Single exposure: Not classified.
STOT - Repeated exposure: Not classified.
Aspiration hazard: Not classified.

Carcinogenic/mutagenic/toxic effects for reproduction

Carcinogenicity: Not classified.
Mutagenicity: Not classified.
Teratogenicity: Not classified.

Additional information on tests

Classification in compliance with the assessment procedure specified in the Regulation (EC) no 1272/2008.

Empirical data on effects on humans

Repeated or prolonged exposure may cause skin irritation and dermatitis, due to degreasing properties of the product.
High concentration of vapours may cause irritation to eyes and respiratory system and produce narcotic effects .
Symptoms of overexposure are dizziness, headache, tiredness, nausea, unconsciousness, cessation of breathing.

SECTION 12: Ecological information

12.1. Toxicity

Ecological data are not available.
Harmful to aquatic life with long lasting effects.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

According to Regulation (EC) No 1907/2006 (REACH) none of the substances, contained in this product are a PBT / vPvB substance.

12.6. Other adverse effects

Hazardous water pollutant.

Further information

Do not flush into surface water or sanitary sewer system.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Where possible recycling is preferred to disposal.
Can be incinerated, when in compliance with local regulations.

Waste disposal number of waste from residues/unused products

200127 MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS; separately collected fractions (except 15 01); paint, inks, adhesives and resins containing dangerous substances
Classified as hazardous waste.

Contaminated packaging

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse.
Packaging that cannot be cleaned should be disposed of like the product.
Empty containers should be taken for local recycling, recovery or waste disposal.

SECTION 14: Transport information

Land transport (ADR/RID)

<u>14.1. UN number:</u>	UN1210
<u>14.2. UN proper shipping name:</u>	PRINTING INK flammable
<u>14.3. Transport hazard class(es):</u>	3
<u>14.4. Packing group:</u>	III
Hazard label:	3

LIFE COLOURS
00336-0003



Classification code: F1
Special Provisions: 163 640E
Limited quantity: 5 L / 30 kg
Transport category: 3
Hazard No: 30
Tunnel restriction code: D/E

Other applicable information (land transport)

Viscous substance - excepted quantity if in containers with a capacity up to 450 l (subsection 2.2.3.1.5 ADR).

Inland waterways transport (ADN)

14.1. UN number: UN1210
14.2. UN proper shipping name: PRINTING INK flammable
14.3. Transport hazard class(es): 3
14.4. Packing group: III
Hazard label: 3



Classification code: F1
Limited quantity: 5 L / 30 kg

Other applicable information (inland waterways transport)

Viscous substance - excepted quantity if in containers with a capacity up to 450 l (subsection 2.2.3.1.5 ADR).

Marine transport (IMDG)

14.1. UN number: UN1210
14.2. UN proper shipping name: PRINTING INK flammable
14.3. Transport hazard class(es): 3
14.4. Packing group: III
Hazard label: 3



Limited quantity: 5 L / 30 kg
EmS: F-E, S-D

Other applicable information (marine transport)

Viscous substance - excepted quantity if in containers with a capacity up to 30 l (subsection 2.3.2.5 IMDG Code).

Air transport (ICAO)

UN/ID number: UN1210
14.2. UN proper shipping name: PRINTING INK flammable
14.3. Transport hazard class(es): 3
14.4. Packing group: III
Hazard label: 3



Limited quantity Passenger: Y344 / 10 L
IATA-packing instructions - Passenger: 355
IATA-max. quantity - Passenger: 60 L
IATA-packing instructions - Cargo: 366
IATA-max. quantity - Cargo: 220 L

14.5. Environmental hazards

LIFE COLOURS

00336-0003

Dangerous for the environment: no

14.6. Special precautions for user

Handle in accordance with good industrial hygiene and safety practice.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

The transport takes place only in approved and appropriate packaging.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

1999/13/EC (VOC): < 60 %

National regulatory information

Employment restrictions: Observe employment restrictions for young people. Observe employment restrictions for child bearing mothers and nursing.

Water contaminating class (D): 2 - water contaminating

15.2. Chemical safety assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Full text of R phrases referred to under Sections 2 and 3

10	Flammable.
20	Harmful by inhalation.
36	Irritating to eyes.
36/37/38	Irritating to eyes, respiratory system and skin.
37	Irritating to respiratory system.
41	Risk of serious damage to eyes.
51	Toxic to aquatic organisms.
52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
53	May cause long-term adverse effects in the aquatic environment.
65	Harmful: may cause lung damage if swallowed.
66	Repeated exposure may cause skin dryness or cracking.
67	Vapours may cause drowsiness and dizziness.

Full text of H statements referred to under Sections 2 and 3

H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Further Information

Data of items 4 to 8, as well as 10 to 12, do partly not refer to the use and the regular employing of the product (in this sense consult information on use and on product), but to liberation of major amounts in case of accidents and irregularities.

The information describes exclusively the safety requirements for the product(s) and is based on the present level of our knowledge.

The delivery specifications are contained in the corresponding product sheet.

This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

(n.a. = not applicable; n.d. = not determined)

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)